

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751443

Luminaire Tested: LD4D65D010-EU4DR3055659027-4LBDP1LI

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P751443  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D65D010-EU4DR3055659027-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6622.9 lumens  
Efficiency: N/A  
Efficacy: 91.0 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P751443  
CATALOG NUMBER: LD4D65D010-EU4DR3055659027-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P751443

CATALOG NUMBER: LD4D65D010-EU4DR3055659027-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96								
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92								
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89								
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85								
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82								
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79								
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77								
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74								
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72								
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1630076	1630076	1630076
5°	1583278	1581426	1583355
10°	1371358	1361689	1371032
15°	894747	889937	885460
20°	444911	461610	444317
25°	224113	252727	219527
30°	89728	97771	78176
35°	41619	39862	33415
40°	17966	19954	16927
45°	12676	15729	12784
50°	4358	11456	4608
55°	2509	4737	2656
60°	1760	2082	1760
65°	1141	1141	1141
70°	694	470	694
75°	0	296	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 15729 cd/sqm



TEST NUMBER: P751443

CATALOG NUMBER: LD4D65D010-EU4DR3055659027-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1872.7	28.3
10°-20°	3015.9	45.5
20°-30°	1303.3	19.7
30°-40°	297.0	4.5
40°-50°	102.0	1.5
50°-60°	24.9	0.4
60°-70°	6.5	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6191.9	93.5
0°-40°	6488.9	98.0
0°-60°	6615.8	99.9
0°-90°	6622.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6622.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	21296	21296	21296	21296	21296	
5°	20606	20586	20582	20625	20607	1874
15°	11291	11155	11230	11194	11174	3023
25°	2654	2754	2992	2684	2599	1270
35°	445	455	427	424	358	302
45°	117	145	145	145	118	83
55°	19	20	36	21	20	18
65°	6	6	6	6	6	6
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P751443

CATALOG NUMBER: LD4D65D010-EU4DR3055659027-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	21296.1	21296.1	21296.1	21296.1	21296.1
2.5°	21154.9	21140.3	21148.6	21159.1	21163.3
5°	20606.0	20586.1	20581.9	20624.8	20607.0
7.5°	19498.7	19470.5	19427.6	19524.9	19615.8
10°	17643.9	17612.5	17519.5	17565.5	17639.7
12.5°	14905.6	14804.1	14802.1	14948.4	14928.6
15°	11291.1	11155.1	11230.4	11193.8	11173.9
17.5°	7592.9	7540.6	7641.0	7610.7	7480.0
20°	5462.0	5475.6	5667.0	5570.8	5454.7
22.5°	3985.7	4034.8	4261.7	4013.9	3923.0
25°	2653.6	2754.0	2992.4	2684.0	2599.3
27.5°	1632.1	1678.1	1919.7	1611.2	1565.2
30°	1015.2	992.2	1106.2	949.4	884.5
32.5°	666.0	636.7	673.3	604.3	552.1
35°	445.4	454.8	426.6	423.5	357.6
37.5°	278.1	319.9	282.3	301.1	230.0
40°	179.8	232.1	199.7	220.6	169.4
42.5°	147.4	178.8	164.2	174.6	150.6
45°	117.1	145.3	145.3	145.3	118.1
47.5°	64.8	97.2	124.4	99.3	69.0
50°	36.6	49.1	96.2	51.2	38.7
52.5°	25.1	28.2	65.9	29.3	26.1
55°	18.8	19.9	35.5	20.9	19.9
57.5°	14.6	15.7	18.8	15.7	14.6
60°	11.5	11.5	13.6	12.5	11.5
62.5°	8.4	8.4	9.4	8.4	8.4
65°	6.3	6.3	6.3	6.3	6.3
67.5°	3.1	4.2	4.2	4.2	4.2
70°	3.1	2.1	2.1	2.1	3.1
72.5°	2.1	1.0	1.0	1.0	1.0
75°	0.0	0.0	1.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)