

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752026

Luminaire Tested: LD4D65D010-EU4DR6555659040-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P752026
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D65D010-EU4DR6555659040-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4594.4 lumens
Efficiency: N/A
Efficacy: 63.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P752026
CATALOG NUMBER: LD4D65D010-EU4DR6555659040-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P752026

CATALOG NUMBER: LD4D65D010-EU4DR6555659040-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69		
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65		
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57		
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	494230
5°	494637
10°	512050
15°	512909
20°	472219
25°	402355
30°	308015
35°	217601
40°	128452
45°	52150
50°	18902
55°	10534
60°	6031
65°	3335
70°	3482
75°	2702
80°	2831
85°	2382

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 52150 cd/sqm



TEST NUMBER: P752026

CATALOG NUMBER: LD4D65D010-EU4DR6555659040-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	435.6	9.5
10°-20°	1256.4	27.3
20°-30°	1507.5	32.8
30°-40°	1013.1	22.1
40°-50°	303.3	6.6
50°-60°	53.5	1.2
60°-70°	15.2	0.3
70°-80°	7.5	0.2
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3199.5	69.6
0°-40°	4212.5	91.7
0°-60°	4569.3	99.5
0°-90°	4594.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4594.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4523	
5°	4510	436
15°	4534	1256
25°	3338	1507
35°	1631	1013
45°	338	303
55°	55	54
65°	13	15
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P752026

CATALOG NUMBER: LD4D65D010-EU4DR6555659040-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4523.4
2.5°	4542.7
5°	4509.9
7.5°	4578.1
10°	4615.3
12.5°	4606.4
15°	4534.4
17.5°	4358.2
20°	4061.3
22.5°	3711.6
25°	3337.5
27.5°	2915.1
30°	2441.4
32.5°	2012.0
35°	1631.4
37.5°	1255.4
40°	900.6
42.5°	588.2
45°	337.5
47.5°	178.7
50°	111.2
52.5°	77.1
55°	55.3
57.5°	39.9
60°	27.6
62.5°	18.0
65°	12.9
67.5°	11.6
70°	10.9
72.5°	8.4
75°	6.4
77.5°	5.8
80°	4.5
82.5°	3.2
85°	1.9
87.5°	1.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)