

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741569

Luminaire Tested: LD4D08D010-EU4DR600210IC9027-4LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P741569  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D08D010-EU4DR600210IC9027-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 762.4 lumens  
Efficiency: N/A  
Efficacy: 85.7 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P741569  
CATALOG NUMBER: LD4D08D010-EU4DR600210IC9027-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P741569

CATALOG NUMBER: LD4D08D010-EU4DR600210IC9027-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86		
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80		
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62		
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	98914
5°	101354
10°	102581
15°	97720
20°	86158
25°	69693
30°	47135
35°	23622
40°	3837
45°	3755
50°	3825
55°	3886
60°	3999
65°	4085
70°	4185
75°	4222
80°	4090
85°	3385

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 4222 cd/sqm



TEST NUMBER: P741569

CATALOG NUMBER: LD4D08D010-EU4DR600210IC9027-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.3	11.6
10°-20°	239.0	31.3
20°-30°	257.1	33.7
30°-40°	111.8	14.7
40°-50°	18.8	2.5
50°-60°	18.2	2.4
60°-70°	15.6	2.0
70°-80°	10.5	1.4
80°-90°	3.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	584.4	76.7
0°-40°	696.1	91.3
0°-60°	733.1	96.2
0°-90°	762.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	762.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	905	
5°	924	88
15°	864	239
25°	578	257
35°	177	112
45°	24	19
55°	20	18
65°	16	16
75°	10	10
85°	3	3
90°	0	



TEST NUMBER: P741569

CATALOG NUMBER: LD4D08D010-EU4DR600210IC9027-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	905.3
2.5°	930.8
5°	924.1
7.5°	926.2
10°	924.6
12.5°	905.5
15°	863.9
17.5°	808.0
20°	741.0
22.5°	669.2
25°	578.1
27.5°	462.3
30°	373.6
32.5°	288.0
35°	177.1
37.5°	75.7
40°	26.9
42.5°	24.8
45°	24.3
47.5°	23.4
50°	22.5
52.5°	21.4
55°	20.4
57.5°	19.3
60°	18.3
62.5°	17.1
65°	15.8
67.5°	14.5
70°	13.1
72.5°	11.6
75°	10.0
77.5°	8.3
80°	6.5
82.5°	4.6
85°	2.7
87.5°	0.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)