

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741738

Luminaire Tested: LD4D08D010-EU4DR700210IC9030-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P741738
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR700210IC9030-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 792.3 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P741738
CATALOG NUMBER: LD4D08D010-EU4DR700210IC9030-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P741738

CATALOG NUMBER: LD4D08D010-EU4DR700210IC9030-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	88	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97329
5°	94433
10°	91808
15°	90594
20°	84600
25°	63557
30°	44927
35°	15913
40°	8372
45°	8916
50°	9230
55°	9410
60°	9462
65°	9255
70°	8753
75°	8105
80°	7173
85°	5767

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 9462 cd/sqm



TEST NUMBER: P741738

CATALOG NUMBER: LD4D08D010-EU4DR700210IC9030-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.2	10.3
10°-20°	222.8	28.1
20°-30°	245.3	31.0
30°-40°	93.7	11.8
40°-50°	44.3	5.6
50°-60°	44.0	5.6
60°-70°	35.2	4.4
70°-80°	20.2	2.6
80°-90°	5.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	549.3	69.3
0°-40°	643.1	81.2
0°-60°	731.3	92.3
0°-90°	792.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	792.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	891	
5°	861	81
15°	801	223
25°	527	245
35°	119	94
45°	58	44
55°	49	44
65°	36	35
75°	19	20
85°	5	5
90°	0	



TEST NUMBER: P741738

CATALOG NUMBER: LD4D08D010-EU4DR700210IC9030-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	890.8
2.5°	881.5
5°	861.0
7.5°	844.0
10°	827.5
12.5°	813.5
15°	800.9
17.5°	770.6
20°	727.6
22.5°	634.8
25°	527.2
27.5°	458.9
30°	356.1
32.5°	230.0
35°	119.3
37.5°	64.5
40°	58.7
42.5°	58.3
45°	57.7
47.5°	56.4
50°	54.3
52.5°	51.9
55°	49.4
57.5°	46.5
60°	43.3
62.5°	39.6
65°	35.8
67.5°	31.6
70°	27.4
72.5°	23.1
75°	19.2
77.5°	15.1
80°	11.4
82.5°	8.0
85°	4.6
87.5°	1.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)