

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741520

Luminaire Tested: LD4D08D010-EU4DR550210IC9035-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P741520
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR550210IC9035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 849.4 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P741520
CATALOG NUMBER: LD4D08D010-EU4DR550210IC9035-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P741520

CATALOG NUMBER: LD4D08D010-EU4DR550210IC9035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	81
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65	65
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61	61
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57	57
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54	54
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104071
5°	99939
10°	99563
15°	96702
20°	86705
25°	71658
30°	54124
35°	39255
40°	25117
45°	11481
50°	3757
55°	1619
60°	699
65°	78
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11481 cd/sqm



TEST NUMBER: P741520

CATALOG NUMBER: LD4D08D010-EU4DR550210IC9035-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.7	10.2
10°-20°	236.6	27.9
20°-30°	269.7	31.7
30°-40°	183.6	21.6
40°-50°	63.3	7.4
50°-60°	8.7	1.0
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	593.0	69.8
0°-40°	776.6	91.4
0°-60°	848.6	99.9
0°-90°	849.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	849.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	952	
5°	911	87
15°	855	237
25°	594	270
35°	294	184
45°	74	63
55°	8	9
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P741520

CATALOG NUMBER: LD4D08D010-EU4DR550210IC9035-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	952.5
2.5°	930.6
5°	911.2
7.5°	901.7
10°	897.4
12.5°	883.2
15°	854.9
17.5°	809.9
20°	745.7
22.5°	671.6
25°	594.4
27.5°	514.0
30°	429.0
32.5°	357.1
35°	294.3
37.5°	234.5
40°	176.1
42.5°	122.0
45°	74.3
47.5°	40.0
50°	22.1
52.5°	13.1
55°	8.5
57.5°	5.4
60°	3.2
62.5°	1.4
65°	0.3
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)