

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741144

Luminaire Tested: LD4D08D010-EU4DR300210IC9040-4LBS1LI

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P741144  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D08D010-EU4DR300210IC9040-4LBS1LI  
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 875.3 lumens  
Efficiency: N/A  
Efficacy: 98.3 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P741144  
CATALOG NUMBER: LD4D08D010-EU4DR300210IC9040-4LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P741144

CATALOG NUMBER: LD4D08D010-EU4DR300210IC9040-4LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	215431	215431	215431
5°	209247	209001	209262
10°	181245	179963	181198
15°	118255	117613	117027
20°	58803	61010	58721
25°	29619	33402	29011
30°	11861	12922	10332
35°	5494	5270	4420
40°	2378	2638	2238
45°	1678	2078	1689
50°	572	1512	607
55°	334	627	347
60°	230	276	230
65°	145	145	145
70°	90	67	90
75°	0	30	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 2078 cd/sqm



TEST NUMBER: P741144

CATALOG NUMBER: LD4D08D010-EU4DR300210IC9040-4LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	247.5	28.3
10°-20°	398.6	45.5
20°-30°	172.2	19.7
30°-40°	39.3	4.5
40°-50°	13.5	1.5
50°-60°	3.3	0.4
60°-70°	0.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	818.3	93.5
0°-40°	857.6	98.0
0°-60°	874.4	99.9
0°-90°	875.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	875.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2814	2814	2814	2814	2814	
5°	2723	2721	2720	2726	2724	248
15°	1492	1474	1484	1479	1477	400
25°	351	364	396	355	344	168
35°	59	60	56	56	47	40
45°	16	19	19	19	16	11
55°	2	3	5	3	3	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P741144

CATALOG NUMBER: LD4D08D010-EU4DR300210IC9040-4LBS1LI

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2814.5	2814.5	2814.5	2814.5	2814.5
2.5°	2795.9	2793.9	2795.0	2796.4	2797.0
5°	2723.3	2720.7	2720.1	2725.8	2723.5
7.5°	2577.0	2573.2	2567.6	2580.5	2592.4
10°	2331.9	2327.7	2315.4	2321.5	2331.3
12.5°	1969.9	1956.5	1956.3	1975.6	1973.0
15°	1492.3	1474.3	1484.2	1479.4	1476.8
17.5°	1003.5	996.6	1009.8	1005.8	988.6
20°	721.9	723.7	749.0	736.2	720.9
22.5°	526.8	533.2	563.2	530.5	518.5
25°	350.7	364.0	395.5	354.7	343.5
27.5°	215.7	221.8	253.7	213.0	206.8
30°	134.2	131.1	146.2	125.5	116.9
32.5°	88.0	84.2	89.0	79.9	72.9
35°	58.8	60.1	56.4	56.0	47.3
37.5°	36.8	42.3	37.3	39.8	30.4
40°	23.8	30.7	26.4	29.2	22.4
42.5°	19.5	23.6	21.7	23.1	19.9
45°	15.5	19.2	19.2	19.2	15.6
47.5°	8.6	12.8	16.4	13.1	9.1
50°	4.8	6.5	12.7	6.8	5.1
52.5°	3.3	3.7	8.7	3.9	3.4
55°	2.5	2.6	4.7	2.8	2.6
57.5°	1.9	2.1	2.5	2.1	1.9
60°	1.5	1.5	1.8	1.7	1.5
62.5°	1.1	1.1	1.3	1.1	1.1
65°	0.8	0.8	0.8	0.8	0.8
67.5°	0.4	0.6	0.6	0.6	0.6
70°	0.4	0.3	0.3	0.3	0.4
72.5°	0.3	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)