

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741157

Luminaire Tested: LD4D08D010-EU4DR300210IC9050-4LBS1LI

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P741157  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D08D010-EU4DR300210IC9050-4LBS1LI  
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 865.0 lumens  
Efficiency: N/A  
Efficacy: 97.2 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P741157  
CATALOG NUMBER: LD4D08D010-EU4DR300210IC9050-4LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P741157

CATALOG NUMBER: LD4D08D010-EU4DR300210IC9050-4LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	212890	212890	212890
5°	206780	206542	206788
10°	179108	177841	179061
15°	116860	116234	115648
20°	58111	60285	58029
25°	29273	33006	28673
30°	11720	12772	10208
35°	5438	5205	4364
40°	2348	2608	2208
45°	1656	2057	1667
50°	572	1489	595
55°	334	614	347
60°	230	276	230
65°	145	145	145
70°	90	67	90
75°	0	30	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 2057 cd/sqm



TEST NUMBER: P741157

CATALOG NUMBER: LD4D08D010-EU4DR300210IC9050-4LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	244.6	28.3
10°-20°	393.9	45.5
20°-30°	170.2	19.7
30°-40°	38.8	4.5
40°-50°	13.3	1.5
50°-60°	3.3	0.4
60°-70°	0.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	808.7	93.5
0°-40°	847.5	98.0
0°-60°	864.1	99.9
0°-90°	865.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	865.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2781	2781	2781	2781	2781	
5°	2691	2689	2688	2694	2691	245
15°	1475	1457	1467	1462	1459	395
25°	347	360	391	350	340	166
35°	58	59	56	55	47	39
45°	15	19	19	19	15	11
55°	2	3	5	3	3	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P741157

CATALOG NUMBER: LD4D08D010-EU4DR300210IC9050-4LBS1LI

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2781.3	2781.3	2781.3	2781.3	2781.3
2.5°	2762.9	2761.0	2762.1	2763.5	2764.0
5°	2691.2	2688.6	2688.1	2693.7	2691.3
7.5°	2546.6	2542.9	2537.3	2550.0	2561.9
10°	2304.4	2300.2	2288.1	2294.1	2303.8
12.5°	1946.7	1933.5	1933.2	1952.3	1949.7
15°	1474.7	1456.9	1466.8	1461.9	1459.4
17.5°	991.7	984.8	997.9	994.0	976.9
20°	713.4	715.2	740.1	727.5	712.4
22.5°	520.5	526.9	556.6	524.2	512.3
25°	346.6	359.7	390.8	350.5	339.5
27.5°	213.1	219.2	250.7	210.4	204.4
30°	132.6	129.6	144.5	124.0	115.5
32.5°	87.0	83.1	87.9	79.0	72.1
35°	58.2	59.4	55.7	55.3	46.7
37.5°	36.3	41.8	36.9	39.3	30.0
40°	23.5	30.3	26.1	28.8	22.1
42.5°	19.3	23.4	21.4	22.8	19.7
45°	15.3	19.0	19.0	19.0	15.4
47.5°	8.5	12.7	16.3	12.9	9.0
50°	4.8	6.4	12.5	6.7	5.0
52.5°	3.3	3.7	8.6	3.8	3.4
55°	2.5	2.6	4.6	2.8	2.6
57.5°	1.9	2.1	2.5	2.1	1.9
60°	1.5	1.5	1.8	1.7	1.5
62.5°	1.1	1.1	1.2	1.1	1.1
65°	0.8	0.8	0.8	0.8	0.8
67.5°	0.4	0.6	0.6	0.6	0.6
70°	0.4	0.3	0.3	0.3	0.4
72.5°	0.3	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)