

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742745

Luminaire Tested: LD4D10D010-EU4DR700210IC9027-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P742745
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D10D010-EU4DR700210IC9027-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 603.5 lumens
Efficiency: N/A
Efficacy: 51.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P742745
CATALOG NUMBER: LD4D10D010-EU4DR700210IC9027-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P742745
 CATALOG NUMBER: LD4D10D010-EU4DR700210IC9027-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74133
5°	71927
10°	69918
15°	69000
20°	64438
25°	48403
30°	34216
35°	12124
40°	6376
45°	6783
50°	7037
55°	7162
60°	7211
65°	7058
70°	6677
75°	6163
80°	5474
85°	4513

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 7219 cd/sqm



TEST NUMBER: P742745

CATALOG NUMBER: LD4D10D010-EU4DR700210IC9027-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.9	10.2
10°-20°	169.7	28.1
20°-30°	186.9	31.0
30°-40°	71.4	11.8
40°-50°	33.7	5.6
50°-60°	33.5	5.6
60°-70°	26.9	4.5
70°-80°	15.4	2.6
80°-90°	4.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	418.4	69.3
0°-40°	489.8	81.2
0°-60°	557.0	92.3
0°-90°	603.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	603.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	678	
5°	656	62
15°	610	170
25°	402	187
35°	91	71
45°	44	34
55°	38	34
65°	27	27
75°	15	15
85°	4	4
90°	0	



TEST NUMBER: P742745
CATALOG NUMBER: LD4D10D010-EU4DR700210IC9027-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	678.5
2.5°	671.4
5°	655.8
7.5°	642.8
10°	630.2
12.5°	619.6
15°	610.0
17.5°	586.9
20°	554.2
22.5°	483.5
25°	401.5
27.5°	349.6
30°	271.2
32.5°	175.2
35°	90.9
37.5°	49.1
40°	44.7
42.5°	44.3
45°	43.9
47.5°	43.0
50°	41.4
52.5°	39.5
55°	37.6
57.5°	35.5
60°	33.0
62.5°	30.2
65°	27.3
67.5°	24.1
70°	20.9
72.5°	17.6
75°	14.6
77.5°	11.5
80°	8.7
82.5°	6.1
85°	3.6
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)