

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745576

Luminaire Tested: LD4D25D010-EU4DR6520359024-4LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P745576  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D25D010-EU4DR6520359024-4LBCSSQMMS  
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1829.3 lumens  
Efficiency: N/A  
Efficacy: 72.9 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P745576

CATALOG NUMBER: LD4D25D010-EU4DR6520359024-4LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P745576

CATALOG NUMBER: LD4D25D010-EU4DR6520359024-4LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	97003
5°	96758
10°	96679
15°	93701
20°	85298
25°	74333
30°	61828
35°	48989
40°	35353
45°	22334
50°	11648
55°	6191
60°	3247
65°	1783
70°	751
75°	835
80°	572
85°	469

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 22334 cd/sqm



TEST NUMBER: P745576

CATALOG NUMBER: LD4D25D010-EU4DR6520359024-4LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	157.1	8.6
10°-20°	430.1	23.5
20°-30°	525.8	28.7
30°-40°	426.6	23.3
40°-50°	212.6	11.6
50°-60°	59.3	3.2
60°-70°	13.5	0.7
70°-80°	3.5	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1113.0	60.8
0°-40°	1539.5	84.2
0°-60°	1811.4	99.0
0°-90°	1829.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1829.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1661	
5°	1650	157
15°	1550	430
25°	1154	526
35°	687	427
45°	270	213
55°	61	59
65°	13	13
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P745576

CATALOG NUMBER: LD4D25D010-EU4DR6520359024-4LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1660.9
2.5°	1659.7
5°	1650.4
7.5°	1645.1
10°	1630.2
12.5°	1599.9
15°	1549.7
17.5°	1471.1
20°	1372.4
22.5°	1266.0
25°	1153.5
27.5°	1033.2
30°	916.8
32.5°	801.8
35°	687.1
37.5°	572.6
40°	463.7
42.5°	361.7
45°	270.4
47.5°	188.4
50°	128.2
52.5°	88.3
55°	60.8
57.5°	41.0
60°	27.8
62.5°	19.3
65°	12.9
67.5°	6.6
70°	4.4
72.5°	4.1
75°	3.7
77.5°	2.5
80°	1.7
82.5°	1.2
85°	0.7
87.5°	0.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)