

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745770

Luminaire Tested: LD4D30D010-EU4DR1515309035-4LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P745770
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR1515309035-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2614.5 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745770
CATALOG NUMBER: LD4D30D010-EU4DR1515309035-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P745770

CATALOG NUMBER: LD4D30D010-EU4DR1515309035-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4008321	4008321	4008321
5°	2355473	2324975	2343369
10°	702998	707925	718758
15°	174860	178274	172767
20°	52317	60590	53430
25°	18447	23495	18681
30°	6777	8918	6889
35°	3391	3834	3282
40°	2145	2358	2145
45°	1582	1687	1582
50°	1259	1259	1259
55°	1051	1051	1051
60°	850	850	850
65°	642	642	642
70°	549	549	549
75°	340	340	454
80°	236	236	236
85°	125	125	125

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 1687 cd/sqm



TEST NUMBER: P745770

CATALOG NUMBER: LD4D30D010-EU4DR1515309035-4LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1695.7	64.9
10°-20°	697.5	26.7
20°-30°	138.5	5.3
30°-40°	34.6	1.3
40°-50°	18.2	0.7
50°-60°	13.5	0.5
60°-70°	9.5	0.4
70°-80°	5.4	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2531.8	96.8
0°-40°	2566.4	98.2
0°-60°	2598.0	99.4
0°-90°	2614.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2614.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	35623	35623	35623	35623	35623	
5°	23177	22939	22877	23036	23058	1693
15°	2013	2051	2052	2016	1989	690
25°	237	268	302	267	240	124
35°	47	50	53	50	45	32
45°	23	23	24	23	23	18
55°	15	15	15	15	15	13
65°	9	9	9	9	9	10
75°	4	4	4	4	6	5
85°	2	2	2	2	2	2
90°	0	0	0	0	0	



TEST NUMBER: P745770

CATALOG NUMBER: LD4D30D010-EU4DR1515309035-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	35623.2	35623.2	35623.2	35623.2	35623.2
2.5°	32133.6	32160.7	32171.3	32202.9	32320.6
5°	23177.2	22939.0	22877.1	23035.5	23058.1
7.5°	13729.3	13777.6	13954.0	13993.2	13851.5
10°	7534.2	7596.1	7587.0	7641.3	7703.1
12.5°	3853.1	3804.8	3789.7	3851.6	3765.6
15°	2013.2	2051.0	2052.5	2016.3	1989.1
17.5°	1082.8	1126.5	1198.9	1140.1	1049.6
20°	639.4	678.6	740.5	692.2	653.0
22.5°	395.1	426.8	470.5	432.8	401.1
25°	236.8	268.4	301.6	266.9	239.8
27.5°	140.2	167.4	188.5	165.9	138.7
30°	90.5	105.6	119.1	104.1	92.0
32.5°	63.3	69.4	75.4	69.4	63.3
35°	46.7	49.8	52.8	49.8	45.2
37.5°	36.2	39.2	40.7	37.7	34.7
40°	30.2	31.7	33.2	31.7	30.2
42.5°	25.6	27.1	27.1	27.1	25.6
45°	22.6	22.6	24.1	22.6	22.6
47.5°	19.6	19.6	21.1	19.6	19.6
50°	18.1	18.1	18.1	18.1	18.1
52.5°	16.6	16.6	16.6	16.6	16.6
55°	15.1	15.1	15.1	15.1	15.1
57.5°	13.6	13.6	13.6	13.6	13.6
60°	12.1	12.1	12.1	12.1	12.1
62.5°	10.6	10.6	10.6	10.6	10.6
65°	9.0	9.0	9.0	9.0	9.0
67.5°	9.0	9.0	9.0	9.0	9.0
70°	7.5	7.5	7.5	7.5	7.5
72.5°	6.0	6.0	6.0	6.0	6.0
75°	4.5	4.5	4.5	4.5	6.0
77.5°	4.5	4.5	4.5	4.5	4.5
80°	3.0	3.0	3.0	3.0	3.0
82.5°	3.0	3.0	3.0	3.0	3.0
85°	1.5	1.5	1.5	1.5	1.5
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)