

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746760

Luminaire Tested: LD4D35BD010-EU4DR3020359027-4LBCSSQMW

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P746760  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D35BD010-EU4DR3020359027-4LBCSSQMW  
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2766.6 lumens  
Efficiency: N/A  
Efficacy: 89.8 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct


Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P746760

CATALOG NUMBER: LD4D35BD010-EU4DR3020359027-4LBCSSQMW

### Luminous Intensity Polar Plot





TEST NUMBER: P746760

CATALOG NUMBER: LD4D35BD010-EU4DR3020359027-4LBCSSQMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	680922	680922	680922
5°	661372	660603	661410
10°	572851	568809	572711
15°	373752	371747	369877
20°	185850	192822	185605
25°	93620	105570	91703
30°	37484	40843	32658
35°	17390	16651	13960
40°	7504	8333	7074
45°	5293	6571	5347
50°	1822	4787	1929
55°	1054	1975	1108
60°	735	873	735
65°	471	471	471
70°	291	201	291
75°	0	118	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 6571 cd/sqm



TEST NUMBER: P746760

CATALOG NUMBER: LD4D35BD010-EU4DR3020359027-4LBCSSQMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	782.3	28.3
10°-20°	1259.8	45.5
20°-30°	544.4	19.7
30°-40°	124.1	4.5
40°-50°	42.6	1.5
50°-60°	10.4	0.4
60°-70°	2.7	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2586.5	93.5
0°-40°	2710.6	98.0
0°-60°	2763.6	99.9
0°-90°	2766.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2766.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	8896	8896	8896	8896	8896	
5°	8608	8599	8598	8616	8608	783
15°	4716	4660	4691	4676	4668	1263
25°	1108	1150	1250	1121	1086	531
35°	186	190	178	177	149	126
45°	49	61	61	61	49	35
55°	8	8	15	9	8	8
65°	3	3	3	3	3	3
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P746760

CATALOG NUMBER: LD4D35BD010-EU4DR3020359027-4LBCSSQMW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	8895.9	8895.9	8895.9	8895.9	8895.9
2.5°	8836.9	8830.8	8834.3	8838.7	8840.4
5°	8607.6	8599.3	8597.6	8615.5	8608.1
7.5°	8145.1	8133.3	8115.4	8156.0	8194.0
10°	7370.3	7357.2	7318.3	7337.5	7368.5
12.5°	6226.4	6184.1	6183.2	6244.3	6236.0
15°	4716.5	4659.8	4691.2	4675.9	4667.6
17.5°	3171.7	3149.9	3191.8	3179.2	3124.6
20°	2281.6	2287.3	2367.2	2327.0	2278.6
22.5°	1664.9	1685.4	1780.2	1676.7	1638.7
25°	1108.5	1150.4	1250.0	1121.2	1085.8
27.5°	681.8	701.0	801.9	673.0	653.8
30°	424.1	414.5	462.1	396.6	369.5
32.5°	278.2	266.0	281.3	252.4	230.6
35°	186.1	190.0	178.2	176.9	149.4
37.5°	116.2	133.6	117.9	125.8	96.1
40°	75.1	97.0	83.4	92.2	70.8
42.5°	61.6	74.7	68.6	72.9	62.9
45°	48.9	60.7	60.7	60.7	49.4
47.5°	27.1	40.6	52.0	41.5	28.8
50°	15.3	20.5	40.2	21.4	16.2
52.5°	10.5	11.8	27.5	12.2	10.9
55°	7.9	8.3	14.8	8.7	8.3
57.5°	6.1	6.6	7.9	6.6	6.1
60°	4.8	4.8	5.7	5.2	4.8
62.5°	3.5	3.5	3.9	3.5	3.5
65°	2.6	2.6	2.6	2.6	2.6
67.5°	1.3	1.7	1.7	1.7	1.7
70°	1.3	0.9	0.9	0.9	1.3
72.5°	0.9	0.4	0.4	0.4	0.4
75°	0.0	0.0	0.4	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)