

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747045

Luminaire Tested: LD4D35BD010-EU4DR4520359050-4LBCSSQMMS

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P747045
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D35BD010-EU4DR4520359050-4LBCSSQMMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3343.7 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P747045
CATALOG NUMBER: LD4D35BD010-EU4DR4520359050-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P747045

CATALOG NUMBER: LD4D35BD010-EU4DR4520359050-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95	95	
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90	90	
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77	77	
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69	69	
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66	66	
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63	63	
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60	60	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	645731
5°	627348
10°	600197
15°	549309
20°	435791
25°	272071
30°	149958
35°	67332
40°	26515
45°	12501
50°	5932
55°	3105
60°	1530
65°	362
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12501 cd/sqm



TEST NUMBER: P747045

CATALOG NUMBER: LD4D35BD010-EU4DR4520359050-4LBCSSQMMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	537.4	16.1
10°-20°	1322.7	39.6
20°-30°	1047.4	31.3
30°-40°	348.8	10.4
40°-50°	69.2	2.1
50°-60°	15.7	0.5
60°-70°	2.3	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2907.6	87.0
0°-40°	3256.4	97.4
0°-60°	3341.4	99.9
0°-90°	3343.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3343.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5910	
5°	5720	537
15°	4856	1323
25°	2257	1047
35°	505	349
45°	81	69
55°	16	16
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P747045

CATALOG NUMBER: LD4D35BD010-EU4DR4520359050-4LBCSSQMMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	5910.0
2.5°	5871.4
5°	5719.9
7.5°	5594.8
10°	5409.8
12.5°	5163.5
15°	4856.2
17.5°	4394.1
20°	3748.0
22.5°	2978.2
25°	2256.8
27.5°	1652.5
30°	1188.6
32.5°	808.4
35°	504.8
37.5°	299.4
40°	185.9
42.5°	122.3
45°	80.9
47.5°	52.1
50°	34.9
52.5°	23.2
55°	16.3
57.5°	10.7
60°	7.0
62.5°	3.7
65°	1.4
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)