

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P747367

Luminaire Tested: LD4D35BD010-EU4DR6520359050-4LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P747367  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D35BD010-EU4DR6520359050-4LBSQW1B  
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2282.8 lumens  
Efficiency: N/A  
Efficacy: 74.1 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 30.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P747367

CATALOG NUMBER: LD4D35BD010-EU4DR6520359050-4LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P747367

CATALOG NUMBER: LD4D35BD010-EU4DR6520359050-4LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	245574
5°	245778
10°	254422
15°	254848
20°	234627
25°	199918
30°	153049
35°	108120
40°	63827
45°	25913
50°	9400
55°	5238
60°	2994
65°	1655
70°	1725
75°	1351
80°	1384
85°	1254

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25913 cd/sqm



TEST NUMBER: P747367

CATALOG NUMBER: LD4D35BD010-EU4DR6520359050-4LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	216.4	9.5
10°-20°	624.3	27.3
20°-30°	749.0	32.8
30°-40°	503.4	22.1
40°-50°	150.7	6.6
50°-60°	26.6	1.2
60°-70°	7.5	0.3
70°-80°	3.7	0.2
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1589.7	69.6
0°-40°	2093.1	91.7
0°-60°	2270.4	99.5
0°-90°	2282.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2282.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2248	
5°	2241	216
15°	2253	624
25°	1658	749
35°	811	503
45°	168	151
55°	28	27
65°	6	8
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P747367

CATALOG NUMBER: LD4D35BD010-EU4DR6520359050-4LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2247.6
2.5°	2257.1
5°	2240.9
7.5°	2274.7
10°	2293.2
12.5°	2288.8
15°	2253.0
17.5°	2165.5
20°	2017.9
22.5°	1844.2
25°	1658.3
27.5°	1448.4
30°	1213.1
32.5°	999.7
35°	810.6
37.5°	623.8
40°	447.5
42.5°	292.2
45°	167.7
47.5°	88.8
50°	55.3
52.5°	38.3
55°	27.5
57.5°	19.8
60°	13.7
62.5°	8.9
65°	6.4
67.5°	5.7
70°	5.4
72.5°	4.2
75°	3.2
77.5°	2.9
80°	2.2
82.5°	1.6
85°	1.0
87.5°	0.6
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)