

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748138

Luminaire Tested: LD4D40BD010-EU4DR6540509050-4LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P748138
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D40BD010-EU4DR6540509050-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3592.4 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 35.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P748138

CATALOG NUMBER: LD4D40BD010-EU4DR6540509050-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P748138
 CATALOG NUMBER: LD4D40BD010-EU4DR6540509050-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	190508
5°	190022
10°	189864
15°	184011
20°	167519
25°	145979
30°	121417
35°	96202
40°	69433
45°	43866
50°	22860
55°	12158
60°	6378
65°	3510
70°	1469
75°	1625
80°	1144
85°	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 43866 cd/sqm



TEST NUMBER: P748138

CATALOG NUMBER: LD4D40BD010-EU4DR6540509050-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	308.5	8.6
10°-20°	844.7	23.5
20°-30°	1032.5	28.7
30°-40°	837.7	23.3
40°-50°	417.5	11.6
50°-60°	116.4	3.2
60°-70°	26.4	0.7
70°-80°	6.9	0.2
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2185.7	60.8
0°-40°	3023.4	84.2
0°-60°	3557.3	99.0
0°-90°	3592.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3592.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3262	
5°	3241	308
15°	3043	845
25°	2265	1033
35°	1349	838
45°	531	417
55°	119	116
65°	25	26
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P748138

CATALOG NUMBER: LD4D40BD010-EU4DR6540509050-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3261.9
2.5°	3259.5
5°	3241.2
7.5°	3230.7
10°	3201.5
12.5°	3142.0
15°	3043.3
17.5°	2888.9
20°	2695.3
22.5°	2486.3
25°	2265.3
27.5°	2029.0
30°	1800.4
32.5°	1574.6
35°	1349.3
37.5°	1124.5
40°	910.7
42.5°	710.4
45°	531.1
47.5°	370.0
50°	251.6
52.5°	173.5
55°	119.4
57.5°	80.5
60°	54.6
62.5°	37.9
65°	25.4
67.5°	12.9
70°	8.6
72.5°	8.1
75°	7.2
77.5°	4.8
80°	3.4
82.5°	2.4
85°	1.4
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)