

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748865

Luminaire Tested: LD4D45BD010-EU4DR6540509027-4LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P748865
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR6540509027-4LBCSSQMMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3519.8 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P748865
CATALOG NUMBER: LD4D45BD010-EU4DR6540509027-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P748865
 CATALOG NUMBER: LD4D45BD010-EU4DR6540509027-4LBCSSQMMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	186653
5°	186182
10°	186022
15°	180286
20°	164131
25°	143028
30°	118956
35°	94256
40°	68030
45°	42983
50°	22406
55°	11903
60°	6249
65°	3441
70°	1451
75°	1580
80°	1110
85°	938

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 42983 cd/sqm



TEST NUMBER: P748865

CATALOG NUMBER: LD4D45BD010-EU4DR6540509027-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	302.2	8.6
10°-20°	827.6	23.5
20°-30°	1011.6	28.7
30°-40°	820.8	23.3
40°-50°	409.0	11.6
50°-60°	114.1	3.2
60°-70°	25.9	0.7
70°-80°	6.7	0.2
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2141.5	60.8
0°-40°	2962.3	84.2
0°-60°	3485.4	99.0
0°-90°	3519.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3519.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3196	
5°	3176	302
15°	2982	828
25°	2220	1012
35°	1322	821
45°	520	409
55°	117	114
65°	25	26
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P748865

CATALOG NUMBER: LD4D45BD010-EU4DR6540509027-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3195.9
2.5°	3193.5
5°	3175.7
7.5°	3165.3
10°	3136.7
12.5°	3078.5
15°	2981.7
17.5°	2830.5
20°	2640.8
22.5°	2436.0
25°	2219.5
27.5°	1988.0
30°	1763.9
32.5°	1542.7
35°	1322.0
37.5°	1101.8
40°	892.3
42.5°	696.0
45°	520.4
47.5°	362.6
50°	246.6
52.5°	170.0
55°	116.9
57.5°	78.9
60°	53.5
62.5°	37.1
65°	24.9
67.5°	12.7
70°	8.5
72.5°	8.0
75°	7.0
77.5°	4.7
80°	3.3
82.5°	2.3
85°	1.4
87.5°	0.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)