

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P748903

Luminaire Tested: LD4D45BD010-EU4DR6540509040-4LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P748903
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D45BD010-EU4DR6540509040-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3835.6 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P748903
CATALOG NUMBER: LD4D45BD010-EU4DR6540509040-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P748903

CATALOG NUMBER: LD4D45BD010-EU4DR6540509040-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	203403
5°	202890
10°	202716
15°	196466
20°	178855
25°	155865
30°	129631
35°	102719
40°	74137
45°	46840
50°	24414
55°	12972
60°	6810
65°	3745
70°	1571
75°	1738
80°	1211
85°	1005

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 46840 cd/sqm



TEST NUMBER: P748903

CATALOG NUMBER: LD4D45BD010-EU4DR6540509040-4LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.4	8.6
10°-20°	901.9	23.5
20°-30°	1102.4	28.7
30°-40°	894.5	23.3
40°-50°	445.8	11.6
50°-60°	124.3	3.2
60°-70°	28.2	0.7
70°-80°	7.4	0.2
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2333.6	60.8
0°-40°	3228.1	84.2
0°-60°	3798.2	99.0
0°-90°	3835.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3835.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3483	
5°	3461	329
15°	3249	902
25°	2419	1102
35°	1441	894
45°	567	446
55°	127	124
65°	27	28
75°	8	7
85°	2	2
90°	0	



TEST NUMBER: P748903

CATALOG NUMBER: LD4D45BD010-EU4DR6540509040-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

0°	
0°	3482.7
2.5°	3480.1
5°	3460.7
7.5°	3449.4
10°	3418.2
12.5°	3354.7
15°	3249.3
17.5°	3084.5
20°	2877.7
22.5°	2654.6
25°	2418.7
27.5°	2166.4
30°	1922.2
32.5°	1681.2
35°	1440.7
37.5°	1200.6
40°	972.4
42.5°	758.5
45°	567.1
47.5°	395.1
50°	268.7
52.5°	185.3
55°	127.4
57.5°	86.0
60°	58.3
62.5°	40.4
65°	27.1
67.5°	13.8
70°	9.2
72.5°	8.7
75°	7.7
77.5°	5.1
80°	3.6
82.5°	2.6
85°	1.5
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)