

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751269

Luminaire Tested: LD4D60D010-EU4DR7055659024-4LBCSSQMB

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P751269
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR7055659024-4LBCSSQMB
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5118.6 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P751269
CATALOG NUMBER: LD4D60D010-EU4DR7055659024-4LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P751269

CATALOG NUMBER: LD4D60D010-EU4DR7055659024-4LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78	78
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71	71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65	65
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60	60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56	56
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	441424
5°	440314
10°	439369
15°	439237
20°	434942
25°	408576
30°	364247
35°	290414
40°	192835
45°	115286
50°	59765
55°	31412
60°	11123
65°	181
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 115286 cd/sqm



TEST NUMBER: P751269

CATALOG NUMBER: LD4D60D010-EU4DR7055659024-4LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	381.8	7.5
10°-20°	1095.0	21.4
20°-30°	1544.7	30.2
30°-40°	1333.5	26.1
40°-50°	597.2	11.7
50°-60°	156.3	3.1
60°-70°	10.2	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3021.5	59.0
0°-40°	4355.0	85.1
0°-60°	5108.5	99.8
0°-90°	5118.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5118.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4040	
5°	4015	382
15°	3883	1095
25°	3389	1545
35°	2177	1333
45°	746	597
55°	165	156
65°	1	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P751269
CATALOG NUMBER: LD4D60D010-EU4DR7055659024-4LBCSSQMB

CANDELA DISTRIBUTION (FULL):

0°	
0°	4040.1
2.5°	4035.7
5°	4014.6
7.5°	3997.2
10°	3960.2
12.5°	3926.7
15°	3883.1
17.5°	3833.0
20°	3740.7
22.5°	3588.9
25°	3389.1
27.5°	3157.4
30°	2887.1
32.5°	2556.6
35°	2177.3
37.5°	1758.9
40°	1352.0
42.5°	1027.3
45°	746.1
47.5°	514.4
50°	351.6
52.5°	242.7
55°	164.9
57.5°	99.5
60°	50.9
62.5°	16.0
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)