

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750864

Luminaire Tested: LD4D60D010-EU4DR4055659040-4LBSQW1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750864
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR4055659040-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5676.3 lumens
Efficiency: N/A
Efficacy: 88.1 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P750864

CATALOG NUMBER: LD4D60D010-EU4DR4055659040-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P750864

CATALOG NUMBER: LD4D60D010-EU4DR4055659040-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96			
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92			
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88			
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84			
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81			
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77			
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74			
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72			
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69			
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1443990
5°	1436970
10°	1358249
15°	1154690
20°	787005
25°	328370
30°	103252
35°	47991
40°	26543
45°	12161
50°	5898
55°	3238
60°	1683
65°	595
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12161 cd/sqm



TEST NUMBER: P750864

CATALOG NUMBER: LD4D60D010-EU4DR4055659040-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1223.4	21.6
10°-20°	2740.7	48.3
20°-30°	1371.9	24.2
30°-40°	251.5	4.4
40°-50°	69.4	1.2
50°-60°	16.3	0.3
60°-70°	3.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5336.0	94.0
0°-40°	5587.4	98.4
0°-60°	5673.1	99.9
0°-90°	5676.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5676.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13216	
5°	13102	###
15°	10208	2741
25°	2724	1372
35°	360	251
45°	79	69
55°	17	16
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750864

CATALOG NUMBER: LD4D60D010-EU4DR4055659040-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	13216.0
2.5°	13196.7
5°	13101.7
7.5°	12799.1
10°	12242.4
12.5°	11374.6
15°	10208.1
17.5°	8691.0
20°	6768.6
22.5°	4614.6
25°	2723.8
27.5°	1439.9
30°	818.4
32.5°	528.9
35°	359.8
37.5°	257.1
40°	186.1
42.5°	127.4
45°	78.7
47.5°	50.2
50°	34.7
52.5°	24.7
55°	17.0
57.5°	10.8
60°	7.7
62.5°	4.6
65°	2.3
67.5°	1.5
70°	0.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)