

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751267

Luminaire Tested: LD4D60D010-EU4DR6555659050-4LBSQW1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P751267  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D60D010-EU4DR6555659050-4LBSQW1B  
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4298.0 lumens  
Efficiency: N/A  
Efficacy: 66.7 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P751267

CATALOG NUMBER: LD4D60D010-EU4DR6555659050-4LBSQW1B

### Luminous Intensity Polar Plot





TEST NUMBER: P751267

CATALOG NUMBER: LD4D60D010-EU4DR6555659050-4LBSQW1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69		
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65		
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57		
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	462359
5°	462743
10°	479033
15°	479823
20°	441756
25°	376400
30°	288145
35°	203569
40°	120166
45°	48781
50°	17678
55°	9848
60°	5660
65°	3102
70°	3258
75°	2533
80°	2643
85°	2257

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 48781 cd/sqm



TEST NUMBER: P751267

CATALOG NUMBER: LD4D60D010-EU4DR6555659050-4LBSQW1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	407.5	9.5
10°-20°	1175.4	27.3
20°-30°	1410.2	32.8
30°-40°	947.7	22.1
40°-50°	283.7	6.6
50°-60°	50.1	1.2
60°-70°	14.2	0.3
70°-80°	7.0	0.2
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2993.1	69.6
0°-40°	3940.8	91.7
0°-60°	4274.6	99.5
0°-90°	4298.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4298.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4232	
5°	4219	407
15°	4242	1175
25°	3122	1410
35°	1526	948
45°	316	284
55°	52	50
65°	12	14
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P751267

CATALOG NUMBER: LD4D60D010-EU4DR6555659050-4LBSQW1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4231.7
2.5°	4249.7
5°	4219.1
7.5°	4282.8
10°	4317.7
12.5°	4309.3
15°	4241.9
17.5°	4077.1
20°	3799.3
22.5°	3472.2
25°	3122.2
27.5°	2727.1
30°	2283.9
32.5°	1882.2
35°	1526.2
37.5°	1174.4
40°	842.5
42.5°	550.2
45°	315.7
47.5°	167.2
50°	104.0
52.5°	72.2
55°	51.7
57.5°	37.3
60°	25.9
62.5°	16.8
65°	12.0
67.5°	10.8
70°	10.2
72.5°	7.8
75°	6.0
77.5°	5.4
80°	4.2
82.5°	3.0
85°	1.8
87.5°	1.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)