

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751592

Luminaire Tested: LD4D65D010-EU4DR4055659024-4LBSQW1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P751592
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D65D010-EU4DR4055659024-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5085.6 lumens
Efficiency: N/A
Efficacy: 69.9 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P751592

CATALOG NUMBER: LD4D65D010-EU4DR4055659024-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P751592

CATALOG NUMBER: LD4D65D010-EU4DR4055659024-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96			
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92			
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88			
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84			
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81			
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77			
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74			
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72			
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69			
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1293724
5°	1287435
10°	1216914
15°	1034528
20°	705102
25°	294205
30°	92503
35°	42989
40°	23776
45°	10909
50°	5286
55°	2895
60°	1508
65°	543
70°	224
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10909 cd/sqm



TEST NUMBER: P751592

CATALOG NUMBER: LD4D65D010-EU4DR4055659024-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1096.1	21.6
10°-20°	2455.5	48.3
20°-30°	1229.1	24.2
30°-40°	225.3	4.4
40°-50°	62.2	1.2
50°-60°	14.6	0.3
60°-70°	2.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4780.7	94.0
0°-40°	5006.0	98.4
0°-60°	5082.7	99.9
0°-90°	5085.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5085.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11841	
5°	11738	###
15°	9146	2455
25°	2440	1229
35°	322	225
45°	71	62
55°	15	15
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P751592

CATALOG NUMBER: LD4D65D010-EU4DR4055659024-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	11840.7
2.5°	11823.4
5°	11738.3
7.5°	11467.2
10°	10968.5
12.5°	10191.0
15°	9145.8
17.5°	7786.6
20°	6064.2
22.5°	4134.4
25°	2440.4
27.5°	1290.0
30°	733.2
32.5°	473.8
35°	322.3
37.5°	230.3
40°	166.7
42.5°	114.1
45°	70.6
47.5°	45.0
50°	31.1
52.5°	22.1
55°	15.2
57.5°	9.7
60°	6.9
62.5°	4.2
65°	2.1
67.5°	1.4
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)