

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751932

Luminaire Tested: LD4D65D010-EU4DR6055659035-4LBCSSQMB

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P751932  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D65D010-EU4DR6055659035-4LBCSSQMB  
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6571.4 lumens  
Efficiency: N/A  
Efficacy: 90.3 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P751932  
CATALOG NUMBER: LD4D65D010-EU4DR6055659035-4LBCSSQMB

### Luminous Intensity Polar Plot





TEST NUMBER: P751932  
 CATALOG NUMBER: LD4D65D010-EU4DR6055659035-4LBCSSQMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87	
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	
6	87	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65	
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61	
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57	
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53	
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50	

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	718521
5°	716768
10°	740577
15°	741345
20°	682115
25°	580187
30°	442077
35°	312622
40°	183579
45°	74076
50°	24732
55°	11906
60°	4895
65°	724
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 74076 cd/sqm



TEST NUMBER: P751932

CATALOG NUMBER: LD4D65D010-EU4DR6055659035-4LBCSSQMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	630.4	9.6
10°-20°	1815.6	27.6
20°-30°	2173.1	33.1
30°-40°	1453.5	22.1
40°-50°	430.9	6.6
50°-60°	62.0	0.9
60°-70°	5.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4619.2	70.3
0°-40°	6072.6	92.4
0°-60°	6565.5	99.9
0°-90°	6571.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6571.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6576	
5°	6535	630
15°	6554	1816
25°	4813	2173
35°	2344	1453
45°	479	431
55°	62	62
65°	3	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P751932

CATALOG NUMBER: LD4D65D010-EU4DR6055659035-4LBCSSQMB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6576.2
2.5°	6567.9
5°	6535.2
7.5°	6623.8
10°	6675.1
12.5°	6665.8
15°	6553.9
17.5°	6289.9
20°	5866.5
22.5°	5358.2
25°	4812.6
27.5°	4197.9
30°	3504.0
32.5°	2884.7
35°	2343.8
37.5°	1801.9
40°	1287.1
42.5°	848.7
45°	479.4
47.5°	245.3
50°	145.5
52.5°	94.2
55°	62.5
57.5°	40.1
60°	22.4
62.5°	9.3
65°	2.8
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)