

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753546

Luminaire Tested: LD4D75BD010-EU4DR6570959027-4LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P753546
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR6570959027-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6237.8 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P753546
CATALOG NUMBER: LD4D75BD010-EU4DR6570959027-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P753546
 CATALOG NUMBER: LD4D75BD010-EU4DR6570959027-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	330782
5°	329953
10°	329670
15°	319505
20°	290872
25°	253474
30°	210821
35°	167044
40°	120567
45°	76170
50°	39706
55°	21098
60°	11085
65°	6094
70°	2561
75°	2821
80°	1951
85°	1675

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 76170 cd/sqm



TEST NUMBER: P753546

CATALOG NUMBER: LD4D75BD010-EU4DR6570959027-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	535.6	8.6
10°-20°	1466.7	23.5
20°-30°	1792.8	28.7
30°-40°	1454.7	23.3
40°-50°	724.9	11.6
50°-60°	202.2	3.2
60°-70°	46.0	0.7
70°-80°	11.9	0.2
80°-90°	3.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3795.1	60.8
0°-40°	5249.8	84.2
0°-60°	6176.9	99.0
0°-90°	6237.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6237.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5664	
5°	5628	536
15°	5284	1467
25°	3933	1793
35°	2343	1455
45°	922	725
55°	207	202
65°	44	46
75°	12	12
85°	2	3
90°	0	



TEST NUMBER: P753546

CATALOG NUMBER: LD4D75BD010-EU4DR6570959027-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5663.7
2.5°	5659.6
5°	5628.0
7.5°	5609.6
10°	5558.9
12.5°	5455.7
15°	5284.2
17.5°	5016.2
20°	4680.0
22.5°	4317.1
25°	3933.4
27.5°	3523.1
30°	3126.1
32.5°	2734.1
35°	2342.9
37.5°	1952.6
40°	1581.4
42.5°	1233.5
45°	922.2
47.5°	642.5
50°	437.0
52.5°	301.3
55°	207.2
57.5°	139.8
60°	94.9
62.5°	65.8
65°	44.1
67.5°	22.5
70°	15.0
72.5°	14.1
75°	12.5
77.5°	8.3
80°	5.8
82.5°	4.2
85°	2.5
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)