

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753676

Luminaire Tested: LD4D75BD010-EU4DR7070959050-4LBCSSQMW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P753676
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR7070959050-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7657.7 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P753676

CATALOG NUMBER: LD4D75BD010-EU4DR7070959050-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P753676

CATALOG NUMBER: LD4D75BD010-EU4DR7070959050-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78	78
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71	71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65	65
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60	60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56	56
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	660383
5°	658738
10°	657312
15°	657131
20°	650698
25°	611255
30°	544925
35°	434481
40°	288497
45°	172473
50°	89409
55°	46994
60°	16629
65°	284
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 172473 cd/sqm



TEST NUMBER: P753676

CATALOG NUMBER: LD4D75BD010-EU4DR7070959050-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	571.2	7.5
10°-20°	1638.1	21.4
20°-30°	2310.9	30.2
30°-40°	1994.9	26.1
40°-50°	893.4	11.7
50°-60°	233.9	3.1
60°-70°	15.2	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4520.3	59.0
0°-40°	6515.2	85.1
0°-60°	7642.5	99.8
0°-90°	7657.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7657.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6044	
5°	6006	571
15°	5809	1638
25°	5070	2311
35°	3257	1995
45°	1116	893
55°	247	234
65°	1	15
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753676

CATALOG NUMBER: LD4D75BD010-EU4DR7070959050-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6044.1
2.5°	6037.6
5°	6006.1
7.5°	5980.0
10°	5924.6
12.5°	5874.6
15°	5809.4
17.5°	5734.4
20°	5596.3
22.5°	5369.2
25°	5070.3
27.5°	4723.6
30°	4319.2
32.5°	3824.7
35°	3257.4
37.5°	2631.3
40°	2022.7
42.5°	1536.8
45°	1116.2
47.5°	769.5
50°	526.0
52.5°	363.0
55°	246.7
57.5°	148.9
60°	76.1
62.5°	23.9
65°	1.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)