

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754364

Luminaire Tested: LD4D80BD010-EU4DR6570959040-4LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P754364
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D80BD010-EU4DR6570959040-4LBCSSQMMMS
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7084.0 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P754364
CATALOG NUMBER: LD4D80BD010-EU4DR6570959040-4LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P754364
 CATALOG NUMBER: LD4D80BD010-EU4DR6570959040-4LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	375654
5°	374703
10°	374386
15°	362845
20°	330326
25°	287854
30°	239415
35°	189702
40°	136921
45°	86502
50°	45085
55°	23969
60°	12592
65°	6924
70°	2903
75°	3204
80°	2220
85°	1876

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 86502 cd/sqm



TEST NUMBER: P754364

CATALOG NUMBER: LD4D80BD010-EU4DR6570959040-4LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	608.3	8.6
10°-20°	1665.7	23.5
20°-30°	2036.0	28.7
30°-40°	1651.9	23.3
40°-50°	823.2	11.6
50°-60°	229.6	3.2
60°-70°	52.2	0.7
70°-80°	13.6	0.2
80°-90°	3.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4309.9	60.8
0°-40°	5961.9	84.2
0°-60°	7014.7	99.0
0°-90°	7084.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7084.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6432	
5°	6391	608
15°	6001	1666
25°	4467	2036
35°	2661	1652
45°	1047	823
55°	235	230
65°	50	52
75°	14	14
85°	3	3
90°	0	



TEST NUMBER: P754364

CATALOG NUMBER: LD4D80BD010-EU4DR6570959040-4LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	6432.0
2.5°	6427.3
5°	6391.3
7.5°	6370.5
10°	6312.9
12.5°	6195.7
15°	6001.0
17.5°	5696.6
20°	5314.8
22.5°	4902.7
25°	4466.9
27.5°	4001.0
30°	3550.1
32.5°	3104.9
35°	2660.7
37.5°	2217.4
40°	1795.9
42.5°	1400.8
45°	1047.3
47.5°	729.7
50°	496.2
52.5°	342.2
55°	235.4
57.5°	158.8
60°	107.8
62.5°	74.7
65°	50.1
67.5°	25.5
70°	17.0
72.5°	16.1
75°	14.2
77.5°	9.5
80°	6.6
82.5°	4.7
85°	2.8
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)