

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754504

Luminaire Tested: LD4D85BD010-EU4DR2570959030-4LBSQW1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P754504
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR2570959030-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5471.3 lumens
Efficiency: N/A
Efficacy: 62.4 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P754504
CATALOG NUMBER: LD4D85BD010-EU4DR2570959030-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P754504

CATALOG NUMBER: LD4D85BD010-EU4DR2570959030-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2267314
5°	2111720
10°	1506351
15°	887184
20°	552017
25°	302945
30°	138540
35°	52473
40°	23762
45°	14293
50°	5932
55°	3829
60°	2666
65°	1810
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14293 cd/sqm



TEST NUMBER: P754504

CATALOG NUMBER: LD4D85BD010-EU4DR2570959030-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1654.7	30.2
10°-20°	2241.2	41.0
20°-30°	1186.0	21.7
30°-40°	292.8	5.4
40°-50°	71.4	1.3
50°-60°	18.8	0.3
60°-70°	6.3	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5081.9	92.9
0°-40°	5374.6	98.2
0°-60°	5464.9	99.9
0°-90°	5471.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5471.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20751	
5°	19254	###
15°	7843	2241
25°	2513	1186
35°	393	293
45°	92	71
55°	20	19
65°	7	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P754504

CATALOG NUMBER: LD4D85BD010-EU4DR2570959030-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	20751.4
2.5°	20410.4
5°	19253.8
7.5°	16930.1
10°	13577.3
12.5°	10263.6
15°	7843.2
17.5°	6112.6
20°	4747.6
22.5°	3560.5
25°	2512.9
27.5°	1685.2
30°	1098.1
32.5°	668.1
35°	393.4
37.5°	240.7
40°	166.6
42.5°	127.3
45°	92.5
47.5°	55.8
50°	34.9
52.5°	25.3
55°	20.1
57.5°	15.7
60°	12.2
62.5°	9.6
65°	7.0
67.5°	2.6
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)