

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756664

Luminaire Tested: LD4D95BD010-EU4DR6570959027-4LBCSSQMB

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P756664  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D95BD010-EU4DR6570959027-4LBCSSQMB  
Description: 4 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7519.6 lumens  
Efficiency: N/A  
Efficacy: 75.8 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 99.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P756664

CATALOG NUMBER: LD4D95BD010-EU4DR6570959027-4LBCSSQMB

### Luminous Intensity Polar Plot





TEST NUMBER: P756664

CATALOG NUMBER: LD4D95BD010-EU4DR6570959027-4LBCSSQMB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	398752
5°	397749
10°	397408
15°	385157
20°	350637
25°	305562
30°	254137
35°	201367
40°	145338
45°	91821
50°	47856
55°	25436
60°	13363
65°	7352
70°	3091
75°	3385
80°	2354
85°	2010

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 91821 cd/sqm



TEST NUMBER: P756664

CATALOG NUMBER: LD4D95BD010-EU4DR6570959027-4LBCSSQMB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	645.7	8.6
10°-20°	1768.1	23.5
20°-30°	2161.2	28.7
30°-40°	1753.5	23.3
40°-50°	873.8	11.6
50°-60°	243.7	3.2
60°-70°	55.4	0.7
70°-80°	14.4	0.2
80°-90°	3.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4575.0	60.8
0°-40°	6328.5	84.2
0°-60°	7446.1	99.0
0°-90°	7519.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7519.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6828	
5°	6784	646
15°	6370	1768
25°	4742	2161
35°	2824	1754
45°	1112	874
55°	250	244
65°	53	55
75°	15	14
85°	3	4
90°	0	



TEST NUMBER: P756664

CATALOG NUMBER: LD4D95BD010-EU4DR6570959027-4LBCSSQMB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6827.5
2.5°	6822.5
5°	6784.4
7.5°	6762.3
10°	6701.1
12.5°	6576.7
15°	6370.0
17.5°	6047.0
20°	5641.6
22.5°	5204.2
25°	4741.7
27.5°	4247.0
30°	3768.4
32.5°	3295.9
35°	2824.3
37.5°	2353.8
40°	1906.3
42.5°	1486.9
45°	1111.7
47.5°	774.6
50°	526.7
52.5°	363.2
55°	249.8
57.5°	168.6
60°	114.4
62.5°	79.3
65°	53.2
67.5°	27.1
70°	18.1
72.5°	17.1
75°	15.0
77.5°	10.0
80°	7.0
82.5°	5.0
85°	3.0
87.5°	2.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)