

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756610

Luminaire Tested: LD4D95BD010-EU4DR6070959030-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P756610
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR6070959030-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7044.9 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P756610
CATALOG NUMBER: LD4D95BD010-EU4DR6070959030-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P756610
 CATALOG NUMBER: LD4D95BD010-EU4DR6070959030-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	914152
5°	936629
10°	947947
15°	903043
20°	796213
25°	643998
30°	435605
35°	218281
40°	35415
45°	34658
50°	35356
55°	35888
60°	36886
65°	37720
70°	38622
75°	39091
80°	37690
85°	31341

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 39091 cd/sqm



TEST NUMBER: P756610

CATALOG NUMBER: LD4D95BD010-EU4DR6070959030-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	816.2	11.6
10°-20°	2208.3	31.3
20°-30°	2375.9	33.7
30°-40°	1032.7	14.7
40°-50°	173.5	2.5
50°-60°	168.7	2.4
60°-70°	144.3	2.0
70°-80°	96.5	1.4
80°-90°	28.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5400.4	76.7
0°-40°	6433.1	91.3
0°-60°	6775.3	96.2
0°-90°	7044.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7044.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8367	
5°	8540	816
15°	7983	2208
25°	5342	2376
35°	1636	1033
45°	224	173
55°	188	169
65°	146	144
75°	93	97
85°	25	29
90°	0	



TEST NUMBER: P756610

CATALOG NUMBER: LD4D95BD010-EU4DR6070959030-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	8366.7
2.5°	8601.9
5°	8539.8
7.5°	8559.4
10°	8544.2
12.5°	8367.8
15°	7983.4
17.5°	7467.3
20°	6847.8
22.5°	6184.7
25°	5341.9
27.5°	4272.6
30°	3452.7
32.5°	2661.1
35°	1636.5
37.5°	700.1
40°	248.3
42.5°	228.7
45°	224.3
47.5°	216.7
50°	208.0
52.5°	198.2
55°	188.4
57.5°	178.6
60°	168.8
62.5°	157.9
65°	145.9
67.5°	133.9
70°	120.9
72.5°	106.7
75°	92.6
77.5°	76.2
80°	59.9
82.5°	42.5
85°	25.0
87.5°	8.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)