

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P778111

Luminaire Tested: LERS4D10D010-EC4DR550210IC9024-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P778111
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LERS4D10D010-EC4DR550210IC9024-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 891.6 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P778111

CATALOG NUMBER: LERS4D10D010-EC4DR550210IC9024-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P778111

CATALOG NUMBER: LERS4D10D010-EC4DR550210IC9024-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	81
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65	65
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61	61
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57	57
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54	54
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	109250
5°	104907
10°	104511
15°	101509
20°	91018
25°	75215
30°	56824
35°	41202
40°	26358
45°	12037
50°	3927
55°	1695
60°	721
65°	78
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12037 cd/sqm



TEST NUMBER: P778111

CATALOG NUMBER: LERS4D10D010-EC4DR550210IC9024-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.0	10.2
10°-20°	248.4	27.9
20°-30°	283.1	31.7
30°-40°	192.7	21.6
40°-50°	66.4	7.4
50°-60°	9.2	1.0
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	622.5	69.8
0°-40°	815.2	91.4
0°-60°	890.8	99.9
0°-90°	891.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	891.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1000	
5°	956	91
15°	897	248
25°	624	283
35°	309	193
45°	78	66
55°	9	9
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P778111

CATALOG NUMBER: LERS4D10D010-EC4DR550210IC9024-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	999.9
2.5°	976.9
5°	956.5
7.5°	946.5
10°	942.0
12.5°	927.1
15°	897.4
17.5°	850.2
20°	782.8
22.5°	705.0
25°	623.9
27.5°	539.6
30°	450.4
32.5°	374.8
35°	308.9
37.5°	246.2
40°	184.8
42.5°	128.1
45°	77.9
47.5°	42.0
50°	23.1
52.5°	13.8
55°	8.9
57.5°	5.7
60°	3.3
62.5°	1.5
65°	0.3
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)