

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760236

Luminaire Tested: LD6D10D010-EU6DR300210IC9050-6LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P760236  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D10D010-EU6DR300210IC9050-6LBS1MW  
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1088.7 lumens  
Efficiency: N/A  
Efficacy: 93.1 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P760236  
CATALOG NUMBER: LD6D10D010-EU6DR300210IC9050-6LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P760236

CATALOG NUMBER: LD6D10D010-EU6DR300210IC9050-6LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	267963	267963	267963
5°	260266	259966	260281
10°	225431	223838	225377
15°	147084	146292	145555
20°	73139	75884	73041
25°	36840	41544	36088
30°	14751	16077	12851
35°	6840	6550	5494
40°	2958	3277	2778
45°	2089	2587	2100
50°	714	1881	762
55°	414	774	440
60°	291	337	291
65°	181	181	181
70°	112	67	112
75°	0	59	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 2587 cd/sqm



TEST NUMBER: P760236

CATALOG NUMBER: LD6D10D010-EU6DR300210IC9050-6LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	307.8	28.3
10°-20°	495.8	45.5
20°-30°	214.2	19.7
30°-40°	48.8	4.5
40°-50°	16.8	1.5
50°-60°	4.1	0.4
60°-70°	1.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1017.9	93.5
0°-40°	1066.7	98.0
0°-60°	1087.6	99.9
0°-90°	1088.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1088.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3501	3501	3501	3501	3501	
5°	3387	3384	3383	3390	3388	308
15°	1856	1834	1846	1840	1837	497
25°	436	453	492	441	427	209
35°	73	75	70	70	59	50
45°	19	24	24	24	19	14
55°	3	3	6	3	3	3
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P760236

CATALOG NUMBER: LD6D10D010-EU6DR300210IC9050-6LBS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3500.8	3500.8	3500.8	3500.8	3500.8
2.5°	3477.6	3475.2	3476.6	3478.3	3479.0
5°	3387.3	3384.1	3383.4	3390.4	3387.5
7.5°	3205.3	3200.7	3193.6	3209.6	3224.6
10°	2900.4	2895.2	2879.9	2887.5	2899.7
12.5°	2450.3	2433.6	2433.3	2457.3	2454.1
15°	1856.1	1833.7	1846.1	1840.1	1836.8
17.5°	1248.2	1239.6	1256.1	1251.1	1229.6
20°	897.9	900.1	931.6	915.7	896.7
22.5°	655.2	663.2	700.5	659.8	644.9
25°	436.2	452.7	491.9	441.2	427.3
27.5°	268.3	275.9	315.6	264.9	257.3
30°	166.9	163.1	181.9	156.1	145.4
32.5°	109.5	104.7	110.7	99.3	90.8
35°	73.2	74.8	70.1	69.6	58.8
37.5°	45.7	52.6	46.4	49.5	37.8
40°	29.6	38.2	32.8	36.3	27.8
42.5°	24.2	29.4	27.0	28.7	24.8
45°	19.3	23.9	23.9	23.9	19.4
47.5°	10.7	16.0	20.5	16.3	11.3
50°	6.0	8.1	15.8	8.4	6.4
52.5°	4.1	4.6	10.8	4.8	4.3
55°	3.1	3.3	5.8	3.4	3.3
57.5°	2.4	2.6	3.1	2.6	2.4
60°	1.9	1.9	2.2	2.1	1.9
62.5°	1.4	1.4	1.5	1.4	1.4
65°	1.0	1.0	1.0	1.0	1.0
67.5°	0.5	0.7	0.7	0.7	0.7
70°	0.5	0.3	0.3	0.3	0.5
72.5°	0.3	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)