

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766376

Luminaire Tested: LD6D45BD010-EU6DR3040509024-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P766376
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR3040509024-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4049.7 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P766376

CATALOG NUMBER: LD6D45BD010-EU6DR3040509024-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P766376

CATALOG NUMBER: LD6D45BD010-EU6DR3040509024-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	996725	996725	996725
5°	968115	966986	968162
10°	838535	832621	838333
15°	547098	544165	541424
20°	272046	282252	271679
25°	137039	154530	134235
30°	54869	59783	47807
35°	25454	24370	20426
40°	10991	12200	10352
45°	7751	9623	7816
50°	2667	7002	2822
55°	1535	2896	1615
60°	1072	1271	1072
65°	688	688	688
70°	425	291	425
75°	0	177	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 9623 cd/sqm



TEST NUMBER: P766376

CATALOG NUMBER: LD6D45BD010-EU6DR3040509024-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1145.1	28.3
10°-20°	1844.1	45.5
20°-30°	796.9	19.7
30°-40°	181.6	4.5
40°-50°	62.4	1.5
50°-60°	15.2	0.4
60°-70°	3.9	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3786.1	93.5
0°-40°	3967.7	98.0
0°-60°	4045.3	99.9
0°-90°	4049.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4049.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	13022	13022	13022	13022	13022	
5°	12600	12588	12585	12611	12600	1146
15°	6904	6821	6867	6845	6832	1849
25°	1623	1684	1830	1641	1589	777
35°	272	278	261	259	219	185
45°	72	89	89	89	72	51
55°	12	12	22	13	12	11
65°	4	4	4	4	4	4
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P766376

CATALOG NUMBER: LD6D45BD010-EU6DR3040509024-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	13021.7	13021.7	13021.7	13021.7	13021.7
2.5°	12935.4	12926.5	12931.6	12938.0	12940.5
5°	12599.8	12587.6	12585.1	12611.3	12600.4
7.5°	11922.7	11905.5	11879.3	11938.7	11994.3
10°	10788.6	10769.4	10712.5	10740.6	10786.0
12.5°	9114.2	9052.2	9050.9	9140.4	9128.2
15°	6904.0	6820.9	6867.0	6844.6	6832.4
17.5°	4642.8	4610.8	4672.2	4653.6	4573.7
20°	3339.8	3348.1	3465.1	3406.3	3335.3
22.5°	2437.1	2467.1	2605.9	2454.4	2398.7
25°	1622.6	1684.0	1829.7	1641.1	1589.4
27.5°	998.0	1026.1	1173.8	985.2	957.1
30°	620.8	606.7	676.4	580.5	540.9
32.5°	407.2	389.3	411.7	369.5	337.6
35°	272.4	278.1	260.8	258.9	218.6
37.5°	170.1	195.6	172.6	184.1	140.7
40°	110.0	141.9	122.1	134.9	103.6
42.5°	90.1	109.3	100.4	106.8	92.1
45°	71.6	88.9	88.9	88.9	72.2
47.5°	39.6	59.5	76.1	60.7	42.2
50°	22.4	30.0	58.8	31.3	23.7
52.5°	15.3	17.3	40.3	17.9	16.0
55°	11.5	12.1	21.7	12.8	12.1
57.5°	9.0	9.6	11.5	9.6	9.0
60°	7.0	7.0	8.3	7.7	7.0
62.5°	5.1	5.1	5.8	5.1	5.1
65°	3.8	3.8	3.8	3.8	3.8
67.5°	1.9	2.6	2.6	2.6	2.6
70°	1.9	1.3	1.3	1.3	1.9
72.5°	1.3	0.6	0.6	0.6	0.6
75°	0.0	0.0	0.6	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)