

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766921

Luminaire Tested: LD6D45BD010-EU6DR6540509024-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P766921
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR6540509024-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3176.8 lumens
Efficiency: N/A
Efficacy: 82.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P766921
CATALOG NUMBER: LD6D45BD010-EU6DR6540509024-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P766921

CATALOG NUMBER: LD6D45BD010-EU6DR6540509024-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69		
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65		
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57		
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	341735
5°	342020
10°	354063
15°	354650
20°	326517
25°	278207
30°	212977
35°	150469
40°	88816
45°	36049
50°	13071
55°	7277
60°	4174
65°	2301
70°	2428
75°	1857
80°	1951
85°	1630

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 36049 cd/sqm



TEST NUMBER: P766921

CATALOG NUMBER: LD6D45BD010-EU6DR6540509024-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	301.2	9.5
10°-20°	868.8	27.3
20°-30°	1042.3	32.8
30°-40°	700.5	22.1
40°-50°	209.7	6.6
50°-60°	37.0	1.2
60°-70°	10.5	0.3
70°-80°	5.2	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2212.3	69.6
0°-40°	2912.8	91.7
0°-60°	3159.5	99.5
0°-90°	3176.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3176.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3128	
5°	3118	301
15°	3135	869
25°	2308	1042
35°	1128	700
45°	233	210
55°	38	37
65°	9	11
75°	4	5
85°	1	2
90°	0	



TEST NUMBER: P766921

CATALOG NUMBER: LD6D45BD010-EU6DR6540509024-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3127.7
2.5°	3141.1
5°	3118.4
7.5°	3165.5
10°	3191.3
12.5°	3185.1
15°	3135.3
17.5°	3013.5
20°	2808.2
22.5°	2566.4
25°	2307.7
27.5°	2015.7
30°	1688.1
32.5°	1391.2
35°	1128.1
37.5°	868.1
40°	622.7
42.5°	406.7
45°	233.3
47.5°	123.6
50°	76.9
52.5°	53.3
55°	38.2
57.5°	27.6
60°	19.1
62.5°	12.4
65°	8.9
67.5°	8.0
70°	7.6
72.5°	5.8
75°	4.4
77.5°	4.0
80°	3.1
82.5°	2.2
85°	1.3
87.5°	0.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)