

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766924

Luminaire Tested: LD6D45BD010-EU6DR6540509024-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P766924
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR6540509024-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4069.5 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P766924

CATALOG NUMBER: LD6D45BD010-EU6DR6540509024-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P766924

CATALOG NUMBER: LD6D45BD010-EU6DR6540509024-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	215802
5°	215261
10°	215075
15°	208444
20°	189763
25°	165370
30°	137542
35°	108979
40°	78658
45°	49689
50°	25904
55°	13767
60°	7230
65°	3980
70°	1673
75°	1828
80°	1278
85°	1072

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 49689 cd/sqm



TEST NUMBER: P766924

CATALOG NUMBER: LD6D45BD010-EU6DR6540509024-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	349.4	8.6
10°-20°	956.9	23.5
20°-30°	1169.6	28.7
30°-40°	949.0	23.3
40°-50°	472.9	11.6
50°-60°	131.9	3.2
60°-70°	30.0	0.7
70°-80°	7.8	0.2
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2476.0	60.8
0°-40°	3425.0	84.2
0°-60°	4029.8	99.0
0°-90°	4069.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4069.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3695	
5°	3672	349
15°	3447	957
25°	2566	1170
35°	1528	949
45°	602	473
55°	135	132
65°	29	30
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P766924

CATALOG NUMBER: LD6D45BD010-EU6DR6540509024-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3695.0
2.5°	3692.3
5°	3671.7
7.5°	3659.7
10°	3626.6
12.5°	3559.3
15°	3447.4
17.5°	3272.6
20°	3053.2
22.5°	2816.5
25°	2566.2
27.5°	2298.5
30°	2039.5
32.5°	1783.7
35°	1528.5
37.5°	1273.8
40°	1031.7
42.5°	804.7
45°	601.6
47.5°	419.2
50°	285.1
52.5°	196.6
55°	135.2
57.5°	91.2
60°	61.9
62.5°	42.9
65°	28.8
67.5°	14.7
70°	9.8
72.5°	9.2
75°	8.1
77.5°	5.4
80°	3.8
82.5°	2.7
85°	1.6
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)