

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766925

Luminaire Tested: LD6D45BD010-EU6DR6540509024-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P766925
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR6540509024-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3682.9 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P766925

CATALOG NUMBER: LD6D45BD010-EU6DR6540509024-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P766925

CATALOG NUMBER: LD6D45BD010-EU6DR6540509024-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	195297
5°	194806
10°	194638
15°	188636
20°	171732
25°	149653
30°	124472
35°	98626
40°	71178
45°	44973
50°	23442
55°	12463
60°	6541
65°	3593
70°	1503
75°	1670
80°	1144
85°	1005

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 44973 cd/sqm



TEST NUMBER: P766925

CATALOG NUMBER: LD6D45BD010-EU6DR6540509024-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	316.2	8.6
10°-20°	866.0	23.5
20°-30°	1058.5	28.7
30°-40°	858.8	23.3
40°-50°	428.0	11.6
50°-60°	119.4	3.2
60°-70°	27.1	0.7
70°-80°	7.1	0.2
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2240.7	60.8
0°-40°	3099.5	84.2
0°-60°	3646.9	99.0
0°-90°	3682.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3682.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3344	
5°	3323	316
15°	3120	866
25°	2322	1058
35°	1383	859
45°	544	428
55°	122	119
65°	26	27
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P766925

CATALOG NUMBER: LD6D45BD010-EU6DR6540509024-6LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3343.9
2.5°	3341.4
5°	3322.8
7.5°	3312.0
10°	3282.0
12.5°	3221.1
15°	3119.8
17.5°	2961.6
20°	2763.1
22.5°	2548.8
25°	2322.3
27.5°	2080.1
30°	1845.7
32.5°	1614.2
35°	1383.3
37.5°	1152.8
40°	933.6
42.5°	728.2
45°	544.5
47.5°	379.4
50°	258.0
52.5°	177.9
55°	122.4
57.5°	82.6
60°	56.0
62.5°	38.8
65°	26.0
67.5°	13.3
70°	8.8
72.5°	8.4
75°	7.4
77.5°	4.9
80°	3.4
82.5°	2.5
85°	1.5
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)