

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766856

Luminaire Tested: LD6D45BD010-EU6DR6040509027-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P766856
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR6040509027-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4322.8 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P766856
CATALOG NUMBER: LD6D45BD010-EU6DR6040509027-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P766856
 CATALOG NUMBER: LD6D45BD010-EU6DR6040509027-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	560934
5°	574724
10°	581669
15°	554117
20°	488567
25°	395158
30°	267290
35°	133943
40°	21723
45°	21262
50°	21689
55°	22021
60°	22639
65°	23139
70°	23704
75°	23978
80°	23092
85°	19306

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 23978 cd/sqm



TEST NUMBER: P766856

CATALOG NUMBER: LD6D45BD010-EU6DR6040509027-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	500.8	11.6
10°-20°	1355.0	31.3
20°-30°	1457.9	33.7
30°-40°	633.7	14.7
40°-50°	106.4	2.5
50°-60°	103.5	2.4
60°-70°	88.5	2.0
70°-80°	59.2	1.4
80°-90°	17.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3313.7	76.7
0°-40°	3947.4	91.3
0°-60°	4157.4	96.2
0°-90°	4322.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4322.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5134	
5°	5240	501
15°	4899	1355
25°	3278	1458
35°	1004	634
45°	138	106
55°	116	104
65°	90	89
75°	57	59
85°	15	18
90°	0	



TEST NUMBER: P766856

CATALOG NUMBER: LD6D45BD010-EU6DR6040509027-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5133.9
2.5°	5278.2
5°	5240.1
7.5°	5252.2
10°	5242.8
12.5°	5134.6
15°	4898.7
17.5°	4582.0
20°	4201.9
22.5°	3795.0
25°	3277.8
27.5°	2621.7
30°	2118.6
32.5°	1632.9
35°	1004.2
37.5°	429.6
40°	152.3
42.5°	140.3
45°	137.6
47.5°	133.0
50°	127.6
52.5°	121.6
55°	115.6
57.5°	109.6
60°	103.6
62.5°	96.9
65°	89.5
67.5°	82.2
70°	74.2
72.5°	65.5
75°	56.8
77.5°	46.8
80°	36.7
82.5°	26.1
85°	15.4
87.5°	5.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)