

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766398

Luminaire Tested: LD6D45BD010-EU6DR3040509030-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P766398
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR3040509030-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3855.3 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P766398

CATALOG NUMBER: LD6D45BD010-EU6DR3040509030-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P766398

CATALOG NUMBER: LD6D45BD010-EU6DR3040509030-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	948886	948886	948886
5°	921645	920569	921691
10°	798282	792655	798095
15°	520844	518047	515440
20°	258989	268706	258647
25°	130460	147114	127791
30°	52235	56911	45509
35°	24230	23202	19455
40°	10462	11611	9852
45°	7383	9158	7448
50°	2536	6669	2679
55°	1468	2762	1548
60°	1026	1209	1026
65°	670	670	670
70°	403	269	403
75°	0	177	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 9158 cd/sqm



TEST NUMBER: P766398

CATALOG NUMBER: LD6D45BD010-EU6DR3040509030-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1090.1	28.3
10°-20°	1755.6	45.5
20°-30°	758.7	19.7
30°-40°	172.9	4.5
40°-50°	59.4	1.5
50°-60°	14.5	0.4
60°-70°	3.8	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3604.4	93.5
0°-40°	3777.3	98.0
0°-60°	3851.2	99.9
0°-90°	3855.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3855.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	12397	12397	12397	12397	12397	
5°	11995	11983	11981	12006	11996	1091
15°	6573	6494	6537	6516	6504	1760
25°	1545	1603	1742	1562	1513	739
35°	259	265	248	246	208	176
45°	68	85	85	85	69	48
55°	11	12	21	12	12	11
65°	4	4	4	4	4	4
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P766398

CATALOG NUMBER: LD6D45BD010-EU6DR3040509030-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	12396.7	12396.7	12396.7	12396.7	12396.7
2.5°	12314.5	12306.0	12310.9	12317.0	12319.4
5°	11995.0	11983.4	11981.0	12005.9	11995.6
7.5°	11350.4	11334.0	11309.1	11365.7	11418.6
10°	10270.7	10252.5	10198.3	10225.1	10268.3
12.5°	8676.7	8617.7	8616.5	8701.7	8690.1
15°	6572.7	6493.5	6537.4	6516.1	6504.5
17.5°	4419.9	4389.5	4447.9	4430.3	4354.2
20°	3179.5	3187.4	3298.8	3242.8	3175.3
22.5°	2320.1	2348.7	2480.8	2336.6	2283.6
25°	1544.7	1603.1	1741.9	1562.4	1513.1
27.5°	950.1	976.9	1117.5	937.9	911.1
30°	591.0	577.6	643.9	552.6	514.9
32.5°	387.7	370.7	392.0	351.8	321.4
35°	259.3	264.8	248.3	246.5	208.2
37.5°	161.9	186.2	164.3	175.3	133.9
40°	104.7	135.1	116.2	128.4	98.6
42.5°	85.8	104.1	95.6	101.6	87.6
45°	68.2	84.6	84.6	84.6	68.8
47.5°	37.7	56.6	72.4	57.8	40.2
50°	21.3	28.6	56.0	29.8	22.5
52.5°	14.6	16.4	38.3	17.0	15.2
55°	11.0	11.6	20.7	12.2	11.6
57.5°	8.5	9.1	11.0	9.1	8.5
60°	6.7	6.7	7.9	7.3	6.7
62.5°	4.9	4.9	5.5	4.9	4.9
65°	3.7	3.7	3.7	3.7	3.7
67.5°	1.8	2.4	2.4	2.4	2.4
70°	1.8	1.2	1.2	1.2	1.8
72.5°	1.2	0.6	0.6	0.6	0.6
75°	0.0	0.0	0.6	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)