

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766951

Luminaire Tested: LD6D45BD010-EU6DR6540509030-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P766951
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR6540509030-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4297.9 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P766951

CATALOG NUMBER: LD6D45BD010-EU6DR6540509030-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P766951

CATALOG NUMBER: LD6D45BD010-EU6DR6540509030-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	227915
5°	227338
10°	227143
15°	220144
20°	200416
25°	174649
30°	145257
35°	115096
40°	83072
45°	52481
50°	27358
55°	14540
60°	7639
65°	4201
70°	1759
75°	1941
80°	1345
85°	1139

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 52481 cd/sqm



TEST NUMBER: P766951

CATALOG NUMBER: LD6D45BD010-EU6DR6540509030-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	369.0	8.6
10°-20°	1010.6	23.5
20°-30°	1235.3	28.7
30°-40°	1002.3	23.3
40°-50°	499.5	11.6
50°-60°	139.3	3.2
60°-70°	31.7	0.7
70°-80°	8.2	0.2
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2614.9	60.8
0°-40°	3617.1	84.2
0°-60°	4255.9	99.0
0°-90°	4297.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4297.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3902	
5°	3878	369
15°	3641	1011
25°	2710	1235
35°	1614	1002
45°	635	499
55°	143	139
65°	30	32
75°	9	8
85°	2	2
90°	0	



TEST NUMBER: P766951

CATALOG NUMBER: LD6D45BD010-EU6DR6540509030-6LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3902.4
2.5°	3899.5
5°	3877.7
7.5°	3865.1
10°	3830.1
12.5°	3759.0
15°	3640.9
17.5°	3456.2
20°	3224.6
22.5°	2974.5
25°	2710.2
27.5°	2427.4
30°	2153.9
32.5°	1883.8
35°	1614.3
37.5°	1345.3
40°	1089.6
42.5°	849.9
45°	635.4
47.5°	442.7
50°	301.1
52.5°	207.6
55°	142.8
57.5°	96.3
60°	65.4
62.5°	45.3
65°	30.4
67.5°	15.5
70°	10.3
72.5°	9.7
75°	8.6
77.5°	5.7
80°	4.0
82.5°	2.9
85°	1.7
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)