

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766976

Luminaire Tested: LD6D45BD010-EU6DR6540509040-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P766976
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR6540509040-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5023.6 lumens
Efficiency: N/A
Efficacy: 129.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P766976
CATALOG NUMBER: LD6D45BD010-EU6DR6540509040-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P766976

CATALOG NUMBER: LD6D45BD010-EU6DR6540509040-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	266398
5°	265727
10°	265496
15°	257311
20°	234251
25°	204138
30°	169784
35°	134525
40°	97093
45°	61344
50°	31974
55°	16994
60°	8924
65°	4906
70°	2066
75°	2279
80°	1581
85°	1340

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 61344 cd/sqm



TEST NUMBER: P766976

CATALOG NUMBER: LD6D45BD010-EU6DR6540509040-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	431.4	8.6
10°-20°	1181.2	23.5
20°-30°	1443.8	28.7
30°-40°	1171.5	23.3
40°-50°	583.8	11.6
50°-60°	162.8	3.2
60°-70°	37.0	0.7
70°-80°	9.6	0.2
80°-90°	2.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3056.4	60.8
0°-40°	4227.9	84.2
0°-60°	4974.5	99.0
0°-90°	5023.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5023.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4561	
5°	4532	431
15°	4256	1181
25°	3168	1444
35°	1887	1171
45°	743	584
55°	167	163
65°	36	37
75°	10	10
85°	2	2
90°	0	



TEST NUMBER: P766976

CATALOG NUMBER: LD6D45BD010-EU6DR6540509040-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4561.3
2.5°	4557.9
5°	4532.5
7.5°	4517.7
10°	4476.8
12.5°	4393.7
15°	4255.6
17.5°	4039.8
20°	3769.0
22.5°	3476.8
25°	3167.8
27.5°	2837.3
30°	2517.6
32.5°	2201.9
35°	1886.8
37.5°	1572.5
40°	1273.5
42.5°	993.4
45°	742.7
47.5°	517.5
50°	351.9
52.5°	242.6
55°	166.9
57.5°	112.6
60°	76.4
62.5°	53.0
65°	35.5
67.5°	18.1
70°	12.1
72.5°	11.4
75°	10.1
77.5°	6.7
80°	4.7
82.5°	3.4
85°	2.0
87.5°	1.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)