

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767052

Luminaire Tested: LD6D45BD010-EU6DR7040509040-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P767052
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR7040509040-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5130.2 lumens
Efficiency: N/A
Efficacy: 132.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P767052

CATALOG NUMBER: LD6D45BD010-EU6DR7040509040-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P767052

CATALOG NUMBER: LD6D45BD010-EU6DR7040509040-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78			
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71			
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65			
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60			
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56			
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51			
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48			
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	442419
5°	441312
10°	440357
15°	440232
20°	435930
25°	409504
30°	365067
35°	291068
40°	193278
45°	115549
50°	59901
55°	31488
60°	11145
65°	181
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 115549 cd/sqm



TEST NUMBER: P767052

CATALOG NUMBER: LD6D45BD010-EU6DR7040509040-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	382.6	7.5
10°-20°	1097.4	21.4
20°-30°	1548.2	30.2
30°-40°	1336.5	26.1
40°-50°	598.5	11.7
50°-60°	156.7	3.1
60°-70°	10.2	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3028.3	59.0
0°-40°	4364.8	85.1
0°-60°	5120.0	99.8
0°-90°	5130.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5130.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4049	
5°	4024	383
15°	3892	1097
25°	3397	1548
35°	2182	1336
45°	748	599
55°	165	157
65°	1	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P767052

CATALOG NUMBER: LD6D45BD010-EU6DR7040509040-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4049.2
2.5°	4044.8
5°	4023.7
7.5°	4006.2
10°	3969.1
12.5°	3935.6
15°	3891.9
17.5°	3841.6
20°	3749.2
22.5°	3597.0
25°	3396.8
27.5°	3164.5
30°	2893.6
32.5°	2562.3
35°	2182.2
37.5°	1762.8
40°	1355.1
42.5°	1029.6
45°	747.8
47.5°	515.5
50°	352.4
52.5°	243.2
55°	165.3
57.5°	99.8
60°	51.0
62.5°	16.0
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)