

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766831

Luminaire Tested: LD6D45BD010-EU6DR5540509050-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P766831
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR5540509050-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5277.5 lumens
Efficiency: N/A
Efficacy: 136.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P766831
CATALOG NUMBER: LD6D45BD010-EU6DR5540509050-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P766831

CATALOG NUMBER: LD6D45BD010-EU6DR5540509050-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	646594
5°	620921
10°	618581
15°	600811
20°	538704
25°	445213
30°	336301
35°	243850
40°	156051
45°	71279
50°	23304
55°	10058
60°	4327
65°	569
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 71279 cd/sqm



TEST NUMBER: P766831

CATALOG NUMBER: LD6D45BD010-EU6DR5540509050-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	538.7	10.2
10°-20°	1470.2	27.9
20°-30°	1675.4	31.7
30°-40°	1140.6	21.6
40°-50°	393.0	7.4
50°-60°	54.3	1.0
60°-70°	5.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3684.4	69.8
0°-40°	4824.9	91.4
0°-60°	5272.3	99.9
0°-90°	5277.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5277.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5918	
5°	5661	539
15°	5312	1470
25°	3693	1675
35°	1828	1141
45°	461	393
55°	53	54
65°	2	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P766831

CATALOG NUMBER: LD6D45BD010-EU6DR5540509050-6LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5917.9
2.5°	5782.3
5°	5661.3
7.5°	5601.9
10°	5575.5
12.5°	5487.5
15°	5311.5
17.5°	5032.1
20°	4633.1
22.5°	4172.6
25°	3693.0
27.5°	3193.6
30°	2665.6
32.5°	2218.3
35°	1828.2
37.5°	1457.1
40°	1094.1
42.5°	758.3
45°	461.3
47.5°	248.6
50°	137.1
52.5°	81.4
55°	52.8
57.5°	33.7
60°	19.8
62.5°	8.8
65°	2.2
67.5°	0.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)