

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768094

Luminaire Tested: LD6D55D010-EU6DR4055659024-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768094
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR4055659024-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6437.6 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P768094
CATALOG NUMBER: LD6D55D010-EU6DR4055659024-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P768094

CATALOG NUMBER: LD6D55D010-EU6DR4055659024-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96		
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88		
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84		
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81		
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77		
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74		
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72		
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69		
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1637622
5°	1629663
10°	1540389
15°	1309533
20°	892534
25°	372409
30°	117092
35°	54420
40°	30095
45°	13798
50°	6697
55°	3676
60°	1923
65°	672
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13798 cd/sqm



TEST NUMBER: P768094

CATALOG NUMBER: LD6D55D010-EU6DR4055659024-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1387.4	21.6
10°-20°	3108.2	48.3
20°-30°	1555.9	24.2
30°-40°	285.2	4.4
40°-50°	78.7	1.2
50°-60°	18.5	0.3
60°-70°	3.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6051.5	94.0
0°-40°	6336.7	98.4
0°-60°	6433.9	99.9
0°-90°	6437.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6437.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14988	
5°	14859	###
15°	11577	3108
25°	3089	1556
35°	408	285
45°	89	79
55°	19	19
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P768094

CATALOG NUMBER: LD6D55D010-EU6DR4055659024-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	14988.2
2.5°	14966.3
5°	14858.6
7.5°	14515.4
10°	13884.1
12.5°	12900.0
15°	11577.0
17.5°	9856.4
20°	7676.2
22.5°	5233.4
25°	3089.1
27.5°	1633.0
30°	928.1
32.5°	599.8
35°	408.0
37.5°	291.6
40°	211.0
42.5°	144.5
45°	89.3
47.5°	56.9
50°	39.4
52.5°	28.0
55°	19.3
57.5°	12.3
60°	8.8
62.5°	5.3
65°	2.6
67.5°	1.8
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)