

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768431

Luminaire Tested: LD6D55D010-EU6DR6055659030-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768431
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR6055659030-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6873.2 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P768431
CATALOG NUMBER: LD6D55D010-EU6DR6055659030-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P768431
 CATALOG NUMBER: LD6D55D010-EU6DR6055659030-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87				
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81				
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75				
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70				
6	87	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65				
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61				
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57				
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53				
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	751528
5°	749694
10°	774594
15°	775392
20°	713439
25°	606830
30°	462389
35°	326974
40°	192008
45°	77475
50°	25871
55°	12458
60°	5113
65°	750
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 77475 cd/sqm



TEST NUMBER: P768431

CATALOG NUMBER: LD6D55D010-EU6DR6055659030-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	659.4	9.6
10°-20°	1899.0	27.6
20°-30°	2272.9	33.1
30°-40°	1520.2	22.1
40°-50°	450.7	6.6
50°-60°	64.8	0.9
60°-70°	6.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4831.3	70.3
0°-40°	6351.5	92.4
0°-60°	6867.1	99.9
0°-90°	6873.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6873.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6878	
5°	6835	659
15°	6855	1899
25°	5034	2273
35°	2451	1520
45°	501	451
55°	65	65
65°	3	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P768431
CATALOG NUMBER: LD6D55D010-EU6DR6055659030-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	6878.3
2.5°	6869.5
5°	6835.4
7.5°	6928.0
10°	6981.7
12.5°	6971.9
15°	6854.9
17.5°	6578.8
20°	6135.9
22.5°	5604.3
25°	5033.6
27.5°	4390.7
30°	3665.0
32.5°	3017.2
35°	2451.4
37.5°	1884.7
40°	1346.2
42.5°	887.7
45°	501.4
47.5°	256.6
50°	152.2
52.5°	98.5
55°	65.4
57.5°	41.9
60°	23.4
62.5°	9.8
65°	2.9
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)