

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768535

Luminaire Tested: LD6D55D010-EU6DR6555659040-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768535
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR6555659040-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6352.6 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P768535
CATALOG NUMBER: LD6D55D010-EU6DR6555659040-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P768535
 CATALOG NUMBER: LD6D55D010-EU6DR6555659040-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	336874
5°	336026
10°	335737
15°	325388
20°	296223
25°	258140
30°	214699
35°	170117
40°	122786
45°	77574
50°	40433
55°	21495
60°	11284
65°	6205
70°	2613
75°	2866
80°	1984
85°	1675

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 77574 cd/sqm



TEST NUMBER: P768535

CATALOG NUMBER: LD6D55D010-EU6DR6555659040-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	545.5	8.6
10°-20°	1493.7	23.5
20°-30°	1825.8	28.7
30°-40°	1481.4	23.3
40°-50°	738.2	11.6
50°-60°	205.9	3.2
60°-70°	46.8	0.7
70°-80°	12.2	0.2
80°-90°	3.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3865.0	60.8
0°-40°	5346.4	84.2
0°-60°	6290.6	99.0
0°-90°	6352.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6352.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5768	
5°	5732	545
15°	5382	1494
25°	4006	1826
35°	2386	1481
45°	939	738
55°	211	206
65°	45	47
75°	13	12
85°	2	3
90°	0	



TEST NUMBER: P768535

CATALOG NUMBER: LD6D55D010-EU6DR6555659040-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	5768.0
2.5°	5763.8
5°	5731.6
7.5°	5712.9
10°	5661.2
12.5°	5556.1
15°	5381.5
17.5°	5108.6
20°	4766.1
22.5°	4396.6
25°	4005.8
27.5°	3587.9
30°	3183.6
32.5°	2784.4
35°	2386.0
37.5°	1988.5
40°	1610.5
42.5°	1256.2
45°	939.2
47.5°	654.4
50°	445.0
52.5°	306.8
55°	211.1
57.5°	142.4
60°	96.6
62.5°	67.0
65°	44.9
67.5°	22.9
70°	15.3
72.5°	14.4
75°	12.7
77.5°	8.5
80°	5.9
82.5°	4.2
85°	2.5
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)