

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768003

Luminaire Tested: LD6D55D010-EU6DR3055659050-6LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P768003  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D55D010-EU6DR3055659050-6LBS1LI  
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7486.7 lumens  
Efficiency: N/A  
Efficacy: 128.6 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct


Input Watts (W): 58.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P768003  
CATALOG NUMBER: LD6D55D010-EU6DR3055659050-6LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P768003

CATALOG NUMBER: LD6D55D010-EU6DR3055659050-6LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1842667	1842667	1842667
5°	1789767	1787677	1789859
10°	1550209	1539273	1549844
15°	1011433	1006005	1000941
20°	502941	521806	502264
25°	253344	285690	248158
30°	101430	110525	88376
35°	47048	45058	37769
40°	20314	22552	19135
45°	14332	17785	14462
50°	4930	12944	5204
55°	2842	5365	3003
60°	1990	2358	1990
65°	1286	1286	1286
70°	783	537	783
75°	0	355	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 17785 cd/sqm



TEST NUMBER: P768003

CATALOG NUMBER: LD6D55D010-EU6DR3055659050-6LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2116.9	28.3
10°-20°	3409.3	45.5
20°-30°	1473.2	19.7
30°-40°	335.8	4.5
40°-50°	115.3	1.5
50°-60°	28.2	0.4
60°-70°	7.3	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6999.4	93.5
0°-40°	7335.2	98.0
0°-60°	7478.7	99.9
0°-90°	7486.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7486.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	24074	24074	24074	24074	24074	
5°	23293	23271	23266	23315	23295	2119
15°	12764	12610	12695	12654	12631	3418
25°	3000	3113	3383	3034	2938	1436
35°	504	514	482	479	404	342
45°	132	164	164	164	134	94
55°	21	22	40	24	22	21
65°	7	7	7	7	7	7
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P768003

CATALOG NUMBER: LD6D55D010-EU6DR3055659050-6LBS1LI

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	24073.5	24073.5	24073.5	24073.5	24073.5
2.5°	23913.9	23897.4	23906.8	23918.6	23923.4
5°	23293.4	23270.9	23266.2	23314.7	23294.6
7.5°	22041.7	22009.8	21961.4	22071.3	22174.1
10°	19945.0	19909.5	19804.3	19856.4	19940.3
12.5°	16849.5	16734.9	16732.5	16898.0	16875.5
15°	12763.6	12610.0	12695.1	12653.7	12631.2
17.5°	8583.1	8524.0	8637.5	8603.2	8455.5
20°	6174.4	6189.7	6406.0	6297.3	6166.1
22.5°	4505.5	4561.1	4817.5	4537.4	4434.6
25°	2999.7	3113.2	3382.7	3034.0	2938.3
27.5°	1845.0	1897.0	2170.0	1821.3	1769.3
30°	1147.6	1121.6	1250.5	1073.2	999.9
32.5°	752.9	719.8	761.2	683.2	624.1
35°	503.5	514.1	482.2	478.7	404.2
37.5°	314.4	361.7	319.1	340.4	260.0
40°	203.3	262.4	225.7	249.4	191.5
42.5°	166.7	202.1	185.6	197.4	170.2
45°	132.4	164.3	164.3	164.3	133.6
47.5°	73.3	109.9	140.6	112.3	78.0
50°	41.4	55.6	108.7	57.9	43.7
52.5°	28.4	31.9	74.5	33.1	29.5
55°	21.3	22.5	40.2	23.6	22.5
57.5°	16.5	17.7	21.3	17.7	16.5
60°	13.0	13.0	15.4	14.2	13.0
62.5°	9.5	9.5	10.6	9.5	9.5
65°	7.1	7.1	7.1	7.1	7.1
67.5°	3.5	4.7	4.7	4.7	4.7
70°	3.5	2.4	2.4	2.4	3.5
72.5°	2.4	1.2	1.2	1.2	1.2
75°	0.0	0.0	1.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)