

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769263

Luminaire Tested: LD6D60D010-EU6DR6555659024-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P769263
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR6555659024-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5658.9 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P769263
CATALOG NUMBER: LD6D60D010-EU6DR6555659024-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P769263
 CATALOG NUMBER: LD6D60D010-EU6DR6555659024-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	300085
5°	299332
10°	299074
15°	289853
20°	263879
25°	229953
30°	191257
35°	151544
40°	109375
45°	69099
50°	36017
55°	19143
60°	10057
65°	5528
70°	2322
75°	2550
80°	1783
85°	1541

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 69099 cd/sqm



TEST NUMBER: P769263

CATALOG NUMBER: LD6D60D010-EU6DR6555659024-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	485.9	8.6
10°-20°	1330.6	23.5
20°-30°	1626.4	28.7
30°-40°	1319.7	23.3
40°-50°	657.6	11.6
50°-60°	183.4	3.2
60°-70°	41.7	0.7
70°-80°	10.8	0.2
80°-90°	2.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3442.9	60.8
0°-40°	4762.6	84.2
0°-60°	5603.6	99.0
0°-90°	5658.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5658.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5138	
5°	5106	486
15°	4794	1331
25°	3568	1626
35°	2126	1320
45°	837	658
55°	188	183
65°	40	42
75°	11	11
85°	2	3
90°	0	



TEST NUMBER: P769263

CATALOG NUMBER: LD6D60D010-EU6DR6555659024-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5138.1
2.5°	5134.4
5°	5105.7
7.5°	5089.1
10°	5043.0
12.5°	4949.4
15°	4793.8
17.5°	4550.7
20°	4245.7
22.5°	3916.5
25°	3568.4
27.5°	3196.1
30°	2836.0
32.5°	2480.4
35°	2125.5
37.5°	1771.4
40°	1434.6
42.5°	1119.0
45°	836.6
47.5°	582.9
50°	396.4
52.5°	273.3
55°	188.0
57.5°	126.8
60°	86.1
62.5°	59.6
65°	40.0
67.5°	20.4
70°	13.6
72.5°	12.8
75°	11.3
77.5°	7.6
80°	5.3
82.5°	3.8
85°	2.3
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)