

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769312

Luminaire Tested: LD6D60D010-EU6DR6555659040-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P769312
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR6555659040-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6968.1 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P769312
CATALOG NUMBER: LD6D60D010-EU6DR6555659040-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P769312

CATALOG NUMBER: LD6D60D010-EU6DR6555659040-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	749594
5°	750209
10°	776624
15°	777915
20°	716194
25°	610242
30°	467158
35°	330042
40°	194818
45°	79082
50°	28676
55°	15963
60°	9156
65°	5041
70°	5303
75°	4095
80°	4279
85°	3636

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 79082 cd/sqm



TEST NUMBER: P769312

CATALOG NUMBER: LD6D60D010-EU6DR6555659040-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	660.6	9.5
10°-20°	1905.6	27.3
20°-30°	2286.3	32.8
30°-40°	1536.5	22.1
40°-50°	460.0	6.6
50°-60°	81.2	1.2
60°-70°	23.1	0.3
70°-80°	11.3	0.2
80°-90°	3.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4852.6	69.6
0°-40°	6389.0	91.7
0°-60°	6930.1	99.5
0°-90°	6968.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6968.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6861	
5°	6840	661
15°	6877	1906
25°	5062	2286
35°	2474	1536
45°	512	460
55°	84	81
65°	20	23
75°	10	11
85°	3	4
90°	0	



TEST NUMBER: P769312

CATALOG NUMBER: LD6D60D010-EU6DR6555659040-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	6860.6
2.5°	6889.9
5°	6840.1
7.5°	6943.5
10°	7000.0
12.5°	6986.4
15°	6877.2
17.5°	6610.1
20°	6159.6
22.5°	5629.3
25°	5061.9
27.5°	4421.3
30°	3702.8
32.5°	3051.5
35°	2474.4
37.5°	1904.0
40°	1365.9
42.5°	892.1
45°	511.8
47.5°	271.0
50°	168.7
52.5°	117.0
55°	83.8
57.5°	60.4
60°	41.9
62.5°	27.3
65°	19.5
67.5°	17.5
70°	16.6
72.5°	12.7
75°	9.7
77.5°	8.8
80°	6.8
82.5°	4.9
85°	2.9
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)