

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769323

Luminaire Tested: LD6D60D010-EU6DR6555659050-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P769323
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D60D010-EU6DR6555659050-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4978.7 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P769323

CATALOG NUMBER: LD6D60D010-EU6DR6555659050-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P769323

CATALOG NUMBER: LD6D60D010-EU6DR6555659050-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	535574
5°	536019
10°	554887
15°	555813
20°	511717
25°	436002
30°	333778
35°	235807
40°	139192
45°	56507
50°	20483
55°	11410
60°	6556
65°	3594
70°	3770
75°	2955
80°	3083
85°	2633

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 56507 cd/sqm



TEST NUMBER: P769323

CATALOG NUMBER: LD6D60D010-EU6DR6555659050-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	472.0	9.5
10°-20°	1361.5	27.3
20°-30°	1633.6	32.8
30°-40°	1097.8	22.1
40°-50°	328.6	6.6
50°-60°	58.0	1.2
60°-70°	16.5	0.3
70°-80°	8.1	0.2
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3467.1	69.6
0°-40°	4564.9	91.7
0°-60°	4951.5	99.5
0°-90°	4978.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4978.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4902	
5°	4887	472
15°	4914	1362
25°	3617	1634
35°	1768	1098
45°	366	329
55°	60	58
65°	14	16
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P769323

CATALOG NUMBER: LD6D60D010-EU6DR6555659050-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4901.8
2.5°	4922.7
5°	4887.2
7.5°	4961.0
10°	5001.4
12.5°	4991.7
15°	4913.7
17.5°	4722.8
20°	4401.0
22.5°	4022.0
25°	3616.6
27.5°	3159.0
30°	2645.6
32.5°	2180.3
35°	1767.9
37.5°	1360.4
40°	975.9
42.5°	637.4
45°	365.7
47.5°	193.6
50°	120.5
52.5°	83.6
55°	59.9
57.5°	43.2
60°	30.0
62.5°	19.5
65°	13.9
67.5°	12.5
70°	11.8
72.5°	9.1
75°	7.0
77.5°	6.3
80°	4.9
82.5°	3.5
85°	2.1
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)