

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770045

Luminaire Tested: LD6D65D010-EU6DR6555659024-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770045
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR6555659024-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5947.2 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P770045
CATALOG NUMBER: LD6D65D010-EU6DR6555659024-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P770045
 CATALOG NUMBER: LD6D65D010-EU6DR6555659024-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	315369
5°	314575
10°	314310
15°	304618
20°	277316
25°	241662
30°	200995
35°	159258
40°	114948
45°	72618
50°	37852
55°	20120
60°	10571
65°	5818
70°	2442
75°	2685
80°	1883
85°	1608

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 72618 cd/sqm



TEST NUMBER: P770045

CATALOG NUMBER: LD6D65D010-EU6DR6555659024-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	510.7	8.6
10°-20°	1398.4	23.5
20°-30°	1709.3	28.7
30°-40°	1386.9	23.3
40°-50°	691.1	11.6
50°-60°	192.8	3.2
60°-70°	43.8	0.7
70°-80°	11.4	0.2
80°-90°	2.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3618.3	60.8
0°-40°	5005.2	84.2
0°-60°	5889.0	99.0
0°-90°	5947.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5947.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5400	
5°	5366	511
15°	5038	1398
25°	3750	1709
35°	2234	1387
45°	879	691
55°	198	193
65°	42	44
75°	12	11
85°	2	3
90°	0	



TEST NUMBER: P770045
CATALOG NUMBER: LD6D65D010-EU6DR6555659024-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5399.8
2.5°	5395.9
5°	5365.7
7.5°	5348.3
10°	5299.9
12.5°	5201.5
15°	5038.0
17.5°	4782.5
20°	4461.9
22.5°	4115.9
25°	3750.1
27.5°	3358.9
30°	2980.4
32.5°	2606.7
35°	2233.7
37.5°	1861.6
40°	1507.7
42.5°	1176.0
45°	879.2
47.5°	612.6
50°	416.6
52.5°	287.3
55°	197.6
57.5°	133.3
60°	90.5
62.5°	62.7
65°	42.1
67.5°	21.4
70°	14.3
72.5°	13.5
75°	11.9
77.5°	7.9
80°	5.6
82.5°	4.0
85°	2.4
87.5°	1.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)