

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769921

Luminaire Tested: LD6D65D010-EU6DR5555659035-6LBDP1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P769921  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D65D010-EU6DR5555659035-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 55° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6451.9 lumens  
Efficiency: N/A  
Efficacy: 88.6 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P769921  
CATALOG NUMBER: LD6D65D010-EU6DR5555659035-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P769921

CATALOG NUMBER: LD6D65D010-EU6DR5555659035-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87	85	82	81
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82	79	77	75
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78	74	71	70
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74	70	67	65
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70	65	62	61
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66	62	58	57
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62	58	55	54
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59	55	52	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	790480
5°	759082
10°	756221
15°	734501
20°	658581
25°	544286
30°	411141
35°	298110
40°	190782
45°	87133
50°	28489
55°	12287
60°	5288
65°	698
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 87133 cd/sqm



TEST NUMBER: P769921

CATALOG NUMBER: LD6D65D010-EU6DR5555659035-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	658.6	10.2
10°-20°	1797.4	27.9
20°-30°	2048.3	31.7
30°-40°	1394.4	21.6
40°-50°	480.5	7.4
50°-60°	66.4	1.0
60°-70°	6.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4504.2	69.8
0°-40°	5898.6	91.4
0°-60°	6445.4	99.9
0°-90°	6451.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6451.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7235	
5°	6921	659
15°	6493	1797
25°	4515	2048
35°	2235	1394
45°	564	480
55°	64	66
65°	3	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P769921

CATALOG NUMBER: LD6D65D010-EU6DR5555659035-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7234.8
2.5°	7068.9
5°	6921.0
7.5°	6848.4
10°	6816.1
12.5°	6708.5
15°	6493.4
17.5°	6151.8
20°	5664.1
22.5°	5101.1
25°	4514.8
27.5°	3904.3
30°	3258.8
32.5°	2711.9
35°	2235.0
37.5°	1781.3
40°	1337.6
42.5°	927.0
45°	563.9
47.5°	303.9
50°	167.6
52.5°	99.5
55°	64.5
57.5°	41.2
60°	24.2
62.5°	10.8
65°	2.7
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)