

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770095

Luminaire Tested: LD6D65D010-EU6DR6555659040-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770095
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR6555659040-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7726.0 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P770095
CATALOG NUMBER: LD6D65D010-EU6DR6555659040-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P770095

CATALOG NUMBER: LD6D65D010-EU6DR6555659040-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	409703
5°	408665
10°	408320
15°	395732
20°	360265
25°	313946
30°	261117
35°	206892
40°	149325
45°	94341
50°	49174
55°	26138
60°	13725
65°	7545
70°	3176
75°	3498
80°	2422
85°	2077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 94341 cd/sqm



TEST NUMBER: P770095

CATALOG NUMBER: LD6D65D010-EU6DR6555659040-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	663.4	8.6
10°-20°	1816.6	23.5
20°-30°	2220.5	28.7
30°-40°	1801.7	23.3
40°-50°	897.8	11.6
50°-60°	250.4	3.2
60°-70°	56.9	0.7
70°-80°	14.8	0.2
80°-90°	3.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4700.5	60.8
0°-40°	6502.2	84.2
0°-60°	7650.4	99.0
0°-90°	7726.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7726.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7015	
5°	6971	663
15°	6545	1817
25°	4872	2221
35°	2902	1802
45°	1142	898
55°	257	250
65°	55	57
75°	16	15
85°	3	4
90°	0	



TEST NUMBER: P770095

CATALOG NUMBER: LD6D65D010-EU6DR6555659040-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	7015.0
2.5°	7009.8
5°	6970.6
7.5°	6947.9
10°	6885.1
12.5°	6757.2
15°	6544.9
17.5°	6212.9
20°	5796.5
22.5°	5347.0
25°	4871.8
27.5°	4363.6
30°	3871.9
32.5°	3386.4
35°	2901.8
37.5°	2418.4
40°	1958.6
42.5°	1527.7
45°	1142.2
47.5°	795.8
50°	541.2
52.5°	373.2
55°	256.7
57.5°	173.2
60°	117.5
62.5°	81.4
65°	54.6
67.5°	27.8
70°	18.6
72.5°	17.5
75°	15.5
77.5°	10.3
80°	7.2
82.5°	5.2
85°	3.1
87.5°	2.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)