

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770096

Luminaire Tested: LD6D65D010-EU6DR6555659040-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770096
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR6555659040-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8112.2 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P770096
CATALOG NUMBER: LD6D65D010-EU6DR6555659040-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P770096

CATALOG NUMBER: LD6D65D010-EU6DR6555659040-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	430185
5°	429102
10°	428733
15°	415516
20°	378276
25°	329644
30°	274173
35°	217238
40°	156797
45°	99057
50°	51636
55°	27442
60°	14414
65°	7932
70°	3330
75°	3656
80°	2556
85°	2144

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 99057 cd/sqm



TEST NUMBER: P770096

CATALOG NUMBER: LD6D65D010-EU6DR6555659040-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	696.6	8.6
10°-20°	1907.4	23.5
20°-30°	2331.6	28.7
30°-40°	1891.8	23.3
40°-50°	942.7	11.6
50°-60°	262.9	3.2
60°-70°	59.8	0.7
70°-80°	15.5	0.2
80°-90°	4.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4935.6	60.8
0°-40°	6827.3	84.2
0°-60°	8033.0	99.0
0°-90°	8112.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8112.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7366	
5°	7319	697
15°	6872	1907
25°	5115	2332
35°	3047	1892
45°	1199	943
55°	270	263
65°	57	60
75°	16	16
85°	3	4
90°	0	



TEST NUMBER: P770096

CATALOG NUMBER: LD6D65D010-EU6DR6555659040-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7365.7
2.5°	7360.3
5°	7319.2
7.5°	7295.3
10°	7229.3
12.5°	7095.1
15°	6872.1
17.5°	6523.6
20°	6086.3
22.5°	5614.4
25°	5115.4
27.5°	4581.8
30°	4065.5
32.5°	3555.7
35°	3046.9
37.5°	2539.3
40°	2056.6
42.5°	1604.1
45°	1199.3
47.5°	835.6
50°	568.3
52.5°	391.8
55°	269.5
57.5°	181.8
60°	123.4
62.5°	85.5
65°	57.4
67.5°	29.2
70°	19.5
72.5°	18.4
75°	16.2
77.5°	10.8
80°	7.6
82.5°	5.4
85°	3.2
87.5°	2.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)